

FLOOR CARE

FINISH

ENDURE

Concrete & Hard Surface Sealer

- Urethane-fortified metal cross-linked sealer
- Optimum durability and protection for hard surfaces and concrete
- Provides superior gloss level with excellent chemical resistance

This specialty sealer provides the optimum of durability and chemical protection for hard surface & concrete. Fortified with urethane and acrylic polymers, produces a protective barrier that resists black marks, scuffs, scratches, and abrasions. Its uncommon durability delivers a classic “wet look” shine that reduces labor by lasting longer between maintenance cycles. This product is ideal for resilient flooring, and may be used on concrete or terrazzo. Maintenance procedures may include spray buffing, high and ultra-high speed burnishing. Outstanding for maintaining difficult “hot spot” floor areas.

DIRECTIONS FOR USE:

This specialty sealer provides the optimum of durability and chemical protection for hard surface & concrete. Fortified with urethane and acrylic polymers, produces a protective barrier that resists black marks, scuffs, scratches, and abrasions. Its uncommon durability delivers a classic “wet look” shine that reduces labor by lasting longer between maintenance cycles. This product is ideal for resilient flooring, and may be used on concrete or terrazzo. Maintenance procedures may include spray buffing, high and ultra-high speed burnishing. Outstanding for maintaining difficult “hot spot” floor areas.

IMPORTANT SAFETY INFORMATION:

KEEP FROM FREEZING

Slip resistance meets or exceeds ASTM D 2047-04 James Machine 0.5 minimum.

PRECAUTIONS:

If medical advice is needed, have the product container or label at hand. Keep out of reach of children. Read the label before use. Store in cool, dry conditions in well-sealed receptacles. Dispose of contents and container in accordance with local, regional, national, and international regulations.

FIRST AID:

IF ON SKIN: Generally the product does not irritate the skin. Rinse with warm water. If skin irritation continues, consult a doctor.

IF IN EYES: Remove contact lenses if worn. Rinse opened eye for several minutes under running water. Then consult a doctor.

IF INHALED: Supply fresh air; consult doctor in case of complaints.

IF SWALLOWED: Do not induce vomiting; call for medical help immediately. Rinse out mouth and then drink plenty of water.

CONTAINS:

Diethylene glycol monoethyl ether (111-90-0), Ammonia, aqueous solution (1336-21-6).



APPLICATIONS

- Nursing homes
- Schools
- Hospitals
- Health care applications

SPECIFICATIONS

Color	White
Fragrance	Acrylic
pH Range	8.0 - 9.0
Form	Liquid
Dilution Range	Ready to Use

PACKAGING

4/1 Gallon	100665-505908
5 Gallon Pail.....	100665-505909
55 Gallon Drum.....	100665-505910

PROP 65 INFO

WARNING: This product can expose you to chemicals including 1,4-dioxane which is known to the State of California to cause Cancer. For more information go to www.P65Warnings.ca.gov.