Page: 1/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

· 1.1 Product identifier

Trade name: Instant Mildew Stain Remover v.3

· Article number: 100329

• 1.2 Relevant identified uses of the substance or mixture and uses advised against No further relevant information available.

· Application of the substance / the mixture: Alkaline cleaner/ detergent

· 1.3 Details of the supplier of the Safety Data Sheet

· Manufacturer/Supplier:

Theochem Laboratories 7373 Rowlett Park Drive Tampa, FL 33610 Phone: 813-237-6463



· 1.4 Emergency telephone number:

ChemTel Inc. (800)255-3924 (North America) +1 (813)248-0585 (International)

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008

Classifications listed are applicable to the OSHA GHS Hazard Communication Standard (29CFR1910.1200).

The following Hazard Statements are applicable only to the EU regulations and not the US GHS regulation: H400, H411.

Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2 H319 Causes serious eye irritation.

Aquatic Acute 1 H400 Very toxic to aquatic life.

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.

· 2.2 Label elements

· Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the Globally Harmonized System within the United States.

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms

The following pictogram(s) are only for use within Europe: GHS09.





GHS07 GHS09

- · Signal word Warning
- · Hazard-determining components of labelling: sodium hydroxide

(Cont'd. on page 2)

Page: 2/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA **GHS**

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 1)

sodium hypochlorite

· Hazard statements

The following Hazard Statements are applicable only to the EU regulations and not the US GHS regulation: H400, H411.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H400 Very toxic to aquatic life.

H411 Toxic to aquatic life with long lasting effects.

· Precautionary statements

P264 Wash thoroughly after handling. P280 Wear protective gloves / eye protection. IF ON SKIN: Wash with plenty of water. P302+P352

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing.

If skin irritation occurs: Get medical advice/attention. P332+P313 P337+P313 If eye irritation persists: Get medical advice/attention.

· NFPA ratings (scale 0 - 4)



Health = 1Fire = 0Reactivity = 0

· HMIS-ratings (scale 0 - 4)



1 Health = 1 Fire = 0

- · 2.3 Other hazards There are no other hazards not otherwise classified that have been identified.
- · Results of PBT and vPvB assessment
- · **PBT**: Not applicable.
- · vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Mixtures

· Components:		
CAS: 7681-52-9 EINECS: 231-668-3 Index number: 017-011-00-1 Reg.nr.: 01-2119488154-34-XXXX	sodium hypochlorite Met. Corr.1, H290; Skin Corr. 1B, H314; Eye Dam. 1, H318 Aquatic Acute 1, H400; Aquatic Chronic 1, H410 TOT SE 3, H335	< 3%
CAS: 1310-73-2 EINECS: 215-185-5 Index number: 011-002-00-6 Reg.nr.: 01-2119457892-27-XXXX	sodium hydroxide Met. Corr.1, H290; Skin Corr. 1A, H314; Eye Dam. 1, H318	< 1%

· Additional information:

For the listed ingredient(s), the identity and/or exact percentages are being withheld as a trade secret. For the wording of the listed Hazard Statements refer to section 16.

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 2)

SECTION 4: First aid measures

· 4.1 Description of first aid measures

- · After inhalation: Supply fresh air; consult doctor in case of complaints.
- · After skin contact:

Immediately remove any clothing soiled by the product.

Rinse with warm water.

If skin irritation continues, consult a doctor.

· After eye contact:

Remove contact lenses if worn.

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· After swallowing:

Rinse out mouth and then drink plenty of water.

Do not induce vomiting; call for medical help immediately.

· 4.2 Most important symptoms and effects, both acute and delayed

Headache

Irritant to skin and mucous membranes.

Causes eye irritation.

Gastric or intestinal disorders when ingested.

Cramp

Coughing

Nausea

- · **Hazards:** Danger of gastric perforation.
- 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- · Suitable extinguishing agents:

The product is not flammable.

Use fire extinguishing methods suitable to surrounding conditions.

- · For safety reasons unsuitable extinguishing agents: None.
- · 5.2 Special hazards arising from the substance or mixture

Formation of toxic gases is possible during heating or in case of fire.

- 5.3 Advice for firefighters
- · Protective equipment:

Wear self-contained respiratory protective device.

Wear fully protective suit.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Use personal protective equipment as required.

For large spills, use respiratory protective device against the effects of fumes/dust/aerosol.

Ensure adequate ventilation

(Cont'd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 3)

Particular danger of slipping on leaked/spilled product.

· 6.2 Environmental precautions

Do not allow product to reach sewage system or any water course.

Inform respective authorities in case of seepage into water course or sewage system.

6.3 Methods and material for containment and cleaning up

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Pick up mechanically.

Send for recovery or disposal in suitable receptacles.

Clean the affected area carefully; suitable cleaners are:

Warm water

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Keep receptacles tightly sealed.

Avoid splashes or spray in enclosed areas.

Use only in well ventilated areas.

Wash hands before breaks and at the end of work.

- · Information about fire and explosion protection: No special measures required.
- · 7.2 Conditions for safe storage, including any incompatibilities
- · Requirements to be met by storerooms and receptacles:

Use only receptacles specifically permitted for this substance/product.

Unsuitable material for receptacle: aluminium.

· Information about storage in one common storage facility:

Store away from foodstuffs.

Do not store together with oxidising and acidic materials.

· Further information about storage conditions:

Store in cool, dry conditions in well sealed receptacles.

Protect from frost.

· 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

· 8.1 Control parameters

6.1 Control parameters				
· Ingredients with limit values that require monitoring at the workplace:				
7681-52-9 sodium hypochlorite				
WEEL (US/	A) Short-term value: 2 mg/m³			
1310-73-2	1310-73-2 sodium hydroxide			
PEL (USA)	Long-term value: 2 mg/m ³			
REL (USA)	Ceiling limit: 2 mg/m³			

(Cont'd. on page 5)

Page: 5/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 4)

TLV (USA)	Ceiling limit: 2 mg/m ³
EL (Canada)	Ceiling limit: 2 mg/m ³
EV (Canada)	Ceiling limit: 2 mg/m³

- DNELs: No further relevant information available.
 PNECs: No further relevant information available.
- · 8.2 Exposure controls
- · General protective and hygienic measures:

The usual precautionary measures are to be adhered to when handling chemicals.

Wash hands before breaks and at the end of work.

Immediately remove all soiled and contaminated clothing.

Avoid contact with the eyes and skin. Do not inhale gases / fumes / aerosols.

Use only in well ventilated areas.

Respiratory protection:

Not required under normal conditions of use.

Use suitable respiratory protective device in case of insufficient ventilation.

For spills, respiratory protection may be advisable.

Protection of hands:



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- For the permanent contact gloves made of the following materials are suitable: Rubber gloves
- · Eye protection:



Safety glasses

- · Body protection: Alkaline resistant protective clothing
- · Limitation and supervision of exposure into the environment:

No further relevant information available.

· Risk management measures: See Section 7 for additional information.

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· Appearance

Form: Liquid

Colour: Clear to straw color.

Odour: Citrus ginger
Odour threshold: Not determined.

pH-value: 12.0 – 13.0
 Melting point/freezing point: Not determined.
 Initial boiling point and boiling range: 100 °C (212 °F)

(Cont'd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

		(Cont'd. from page 5)
· Flash point:	Not applicable.	
· Flammability (solid, gas):	Not applicable.	
· Auto/Self-ignition temperature:	Not determined.	
· Decomposition temperature:	Not determined.	
· Explosive properties:	Product does not present an explosion hazard.	
· Explosion limits Lower: Upper:	Not determined. Not determined.	
· Vapour pressure:	Not determined.	
 Density: Relative density: Vapour density: Evaporation rate: 	1.05 – 1.06 Not determined. Not determined.	
· Solubility in / Miscibility with water:	Soluble.	
· Partition coefficient: n-octanol/water: Not determined.		
ViscosityDynamic:Kinematic:9.2 Other information	Not determined. Not determined. No further relevant information available.	

SECTION 10: Stability and reactivity

- · 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided:

No decomposition if used and stored according to specifications.

· 10.3 Possibility of hazardous reactions

Toxic fumes may be released if heated above the decomposition point.

Reacts with many consumer products, releasing chlorine or chlorine oxide gas.

Reacts with strong acids and oxidising agents.

Corrodes aluminium.

- · 10.4 Conditions to avoid Excessive heat.
- · 10.5 Incompatible materials

Warning! Do not use together with other products. May release dangerous gases (chlorine).

· 10.6 Hazardous decomposition products

Chlorine

Chlorine compounds

Page: 7/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 5)

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity: Based on available data, the classification criteria are not met.
- · LD/LC50 values relevant for classification:

7681-52-9 sodium hypochlorite

Oral LD50 5800 mg/kg (mouse)

- Primary irritant effect
- · Skin corrosion/irritation:

Causes skin irritation.

· Serious eye damage/irritation:

Causes serious eye irritation.

- · Respiratory or skin sensitisation: Based on available data, the classification criteria are not met.
- · Carcinogenic categories
- · IARC (International Agency for Research on Cancer):

None of the ingredients are listed.

· NTP (National Toxicology Program):

None of the ingredients are listed.

· OSHA-Ca (Occupational Safety & Health Administration):

None of the ingredients are listed.

· Probable routes of exposure:

Ingestion.

Skin contact.

Eye contact.

- · Germ cell mutagenicity: Based on available data, the classification criteria are not met.
- · Carcinogenicity: Based on available data, the classification criteria are not met.
- · Reproductive toxicity: Based on available data, the classification criteria are not met.
- · STOT-single exposure: Based on available data, the classification criteria are not met.
- · STOT-repeated exposure: Based on available data, the classification criteria are not met.
- · Aspiration hazard: Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: Toxic to aquatic life with long lasting effects.
- · 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Additional ecological information:
- · General notes:

Do not allow product to reach ground water, water course or sewage system.

Due to available data on eliminability/decomposition and bioaccumulation potential prolonged term damage of the environment can not be excluded.

Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A (Cont'd. on page 8)

Page: 8/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 7)

high pH-value harms aquatic organisms. If the dilution of the use-level pH-value is considerably reduced, the aqueous waste, emptied into drains, is only low water-dangerous.

- · 12.5 Results of PBT and vPvB assessment
- · **PBT:** Not applicable.
- · **vPvB:** Not applicable.
- · 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation

The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.

- · Uncleaned packaging:
- · Recommendation: Disposal must be made according to official regulations.

SECTION 14: Transport information		
· 14.1 UN-Number		
· DOT	Not Regulated	
· ADR, IMDG, IATA	UN3082	
· 14.2 UN proper shipping name		
· DOT	Not Regulated	
· ADR, IMDG	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (SODIUM HYPOCHLORITE)	
·IATA	Environmentally hazardous substance, liquid, n.o.s. (sodium hypochlorite)	
· 14.3 Transport hazard class(es)		
· DOT		
· Class	Not Regulated	
· ADR		
· Class	9 (M6) Miscellaneous dangerous substances and articles.	
· Label	9	
(Cont'd. on pag		

Page: 9/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 8) · IMDG, IATA · Class 9 Miscellaneous dangerous substances and articles. · Label 9 · 14.4 Packing group · DOT Not Regulated · ADR, IMDG, IATA Ш · 14.5 Environmental hazards: · Marine pollutant: Yes · 14.6 Special precautions for user Warning: Miscellaneous dangerous substances and articles. Danger code (Kemler): 90 · EMS Number: F-A,S-F · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code Not applicable. · Transport/Additional information: Not regulated when carried in single or combination packaging containing a net quantity of 5 L or less for liquids or 5 kg or less for solids per the following: DOT: 171.4(c)(2) ADR: SP 375 IMDG: 2.10.2.7 IATA: special provision A197 · DOT Transport labeling is not required for non-bulk single package shipments by motor vehicle, rail car or aircraft. Bulk packaging consists of a maximum capacity of greater than 450L (119 gallons) for a liquid and a maximum net mass greater than 400kg (882 pounds) for a solid.

SECTION 15: Regulatory information

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- · United States (USA)
- ·SARA

(Cont'd. on page 10)

Page: 10/11

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 9)

· Section 355 (extremely hazardous substances):

None of the ingredients are listed.

· Section 313 (Specific toxic chemical listings):

None of the ingredients are listed.

· TSCA (Toxic Substances Control Act):

All ingredients are listed.

- · Proposition 65 (California):
- · Chemicals known to cause cancer:

None of the ingredients are listed.

· Chemicals known to cause reproductive toxicity for females:

None of the ingredients are listed.

· Chemicals known to cause reproductive toxicity for males:

None of the ingredients are listed.

· Chemicals known to cause developmental toxicity:

None of the ingredients are listed.

· EPA (Environmental Protection Agency)

None of the ingredients are listed.

· IARC (International Agency for Research on Cancer)

None of the ingredients are listed.

· NIOSH-Ca (National Institute for Occupational Safety and Health)

None of the ingredients are listed.

Canadian Domestic Substances List (DSL)

All ingredients are listed.

- · Other regulations, limitations and prohibitive regulations
- · Substances of very high concern (SVHC) according to REACH, Article 57

None of the ingredients are listed.

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H290 May be corrosive to metals.

H314 Causes severe skin burns and eye damage.

H318 Causes serious eve damage.

H335 May cause respiratory irritation.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

· Abbreviations and acronyms:

(Cont'd. on page 11)

Page: 11/11

Safety Data Sheet according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA GHS

Printing date: 11 May 2022 Revision: 15 December 2017

Trade name: Instant Mildew Stain Remover v.3

(Cont'd. from page 10)

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistant, Bio-accumulable, Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Met. Corr.1: Corrosive to metals - Category 1

Skin Corr. 1A: Skin corrosion/irritation - Category 1A

Skin Corr. 1B: Skin corrosion/irritation - Category 1B

Skin Irrit. 2: Skin corrosion/irritation - Category 2

Eye Dam. 1: Serious eye damage/eye irritation - Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) - Category 3

Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard - Category 1

Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard - Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard - Category 2

Sources

Website, European Chemicals Agency (echa.europa.eu)

Website, US EPA Substance Registry Services (ofmpub.epa.gov/sor internet/registry/substreg/home/overview/home.do)

Website, Chemical Abstracts Registry, American Chemical Society (www.cas.org)

Patty's Industrial Hygiene, 6th ed., Rose, Vernon, ed. ISBN: 978-0-470-07488-6

Casarett and Doull's Toxicology: The Basic Science of Poisons, 8th Ed., Klaasen, Curtis D., ed., ISBN: 978-0-07-176923-5.

Safety Data Sheets, Individual Manufacturers