

Safety Data Sheet
 according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
 OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

- **1.1 Product identifier**
- Trade name: **Pink Hi-Active Beads v.7**
- Article number: 100139; 200108
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
 No further relevant information available.
- **Application of the substance / the mixture** Detergents
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
 Theochem Laboratories
 7373 Rowlett Park Drive
 Tampa, FL 33610
 Phone: 813-237-6463
- **1.4 Emergency telephone number:**
 ChemTel Inc.
 (800)255-3924, +1 (813)248-0585



SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
 Classifications listed also are applicable to the OSHA GHS Hazard Communication Standard (29CFR1910.1200).



Skin Irrit. 2 H315 Causes skin irritation.
 Eye Irrit. 2 H319 Causes serious eye irritation.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xi; Irritant

R36/38: Irritating to eyes and skin.

- **Information concerning particular hazards for human and environment:**
 The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.
- **Classification system:**
 The classification is according to the latest editions of the EU-lists, and extended by company and literature data.
 The classification is in accordance with the latest editions of international substances lists, and is supplemented by information from technical literature and by information provided by the company.

- **2.2 Label elements**

- **Labelling according to Regulation (EC) No 1272/2008**

The substance is classified and labelled according to the Globally Harmonized System within the United States (GHS).

The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 1)

- **Hazard pictograms**



GHS07

- **Signal word** Warning

- **Hazard-determining components of labelling:**

disodium metasilicate

- **Hazard statements**

H315 Causes skin irritation.

H319 Causes serious eye irritation.

- **Precautionary statements**

P280 Wear protective gloves / eye protection.

P264 Wash thoroughly after handling.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P332+P313 If skin irritation occurs: Get medical advice/attention.

P337+P313 If eye irritation persists: Get medical advice/attention.

P302+P352 IF ON SKIN: Wash with plenty of water.

- **Hazard description:**

- **WHMIS-symbols:**

D2B - Toxic material causing other toxic effects



- **NFPA ratings (scale 0 - 4)**



Health = 1

Fire = 0

Reactivity = 0

- **HMIS-ratings (scale 0 - 4)**



Health = 1

Fire = 0

Reactivity = 0

- **HMIS Long Term Health Hazard Substances**

None of the ingredients are listed.

- **2.3 Other hazards**

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

(Contd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7





(Contd. of page 2)

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**

- **Description:** Mixture of substances listed below with nonhazardous additions.

- **Dangerous components:**

CAS: 497-19-8 EINECS: 207-838-8 Index number: 011-005-00-2	sodium carbonate Xi R36 Eye Irrit. 2, H319	10-25%
CAS: 25155-30-0 EINECS: 246-680-4	sodium dodecylbenzenesulphonate  Xn R22; Xi R38-41  Eye Dam. 1, H318 Acute Tox. 4, H302; Skin Irrit. 2, H315	<10%
CAS: 6834-92-0 EINECS: 229-912-9 Index number: 014-010-00-8	disodium metasilicate  C R34; Xi R37  Met. Corr. 1, H290; Skin Corr. 1B, H314 STOT SE 3, H335	<10%
• Additional information: For the wording of the listed risk phrases refer to section 16.		

SECTION 4: First aid measures

- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**
Immediately rinse with water.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
Nausea
Cramp
Coughing
Dizziness
- **Hazards** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
If necessary oxygen respiration treatment.
Medical supervision for at least 48 hours.

(Contd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 3)

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** None.
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.
- **Additional information** Cool endangered receptacles with water fog or haze.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Product forms slippery surface when combined with water.
Ensure adequate ventilation
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Pick up mechanically.
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Prevent formation of dust.
Avoid breathing dust.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Protect from humidity and water.
Avoid storage near extreme heat, ignition sources or open flame.
- **Information about storage in one common storage facility:**
Store away from foodstuffs.
Store away from oxidising agents.
- **Further information about storage conditions:**
Store in cool, dry conditions in well sealed receptacles.

(Contd. on page 5)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 4)

Keep container tightly sealed.

This product is hygroscopic.

Protect from humidity and water.

- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **DNELs** No further relevant information available.
- **PNECs** No further relevant information available.
- **Additional information:** The lists valid during the making were used as basis.

- **8.2 Exposure controls**

- **Personal protective equipment:**

- **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

- **Respiratory protection:**

Not required under normal conditions of use.

For spills, respiratory protection may be advisable.

- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation.

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **For the permanent contact gloves made of the following materials are suitable:**

Butyl rubber, BR

Neoprene gloves

(Contd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 5)

- **Eye protection:**



Safety glasses

- **Body protection:**

Protection may be required for spills.
Not required under normal conditions of use.

- **Limitation and supervision of exposure into the environment**

No further relevant information available.

- **Risk management measures**

See Section 7 for additional information.
No further relevant information available.

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

Form: Beads

Colour: Pink

- Odour: Citrus.

- **Odour threshold:** Not determined.

- **pH-value at 20 °C:** <11.0 (1% solution)

- **Change in condition**

Melting point/Melting range: Not Determined.

Boiling point/Boiling range: Undetermined.

- **Flash point:** Not applicable.

- **Flammability (solid, gaseous):** Not determined.

- **Auto/Self-ignition temperature:** Not determined.

- **Decomposition temperature:** Not determined.

- **Self-igniting:** Product is not self-igniting.

- **Danger of explosion:** Product does not present an explosion hazard.

- **Explosion limits:**

Lower: Not determined.

Upper: Not determined.

- **Vapour pressure at 20 °C:** 23 hPa

- **Density at 20 °C:** 0.5 g/cm³

- **Relative density** Not determined.

- **Vapour density** Not applicable.

- **Evaporation rate** Not applicable.

(Contd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 6)

- **Solubility in / Miscibility with water:** Soluble.
- **Partition coefficient (n-octanol/water):** Not determined.
- **Viscosity:**
 - Dynamic:** Not applicable.
 - Kinematic:** Not applicable.
- **Solvent content:**
 - Organic solvents:** Not determined.
- **Solids content:** Not determined.
- **9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **10.3 Possibility of hazardous reactions**
Strong exothermic reaction with acids.
As the product is supplied it is not capable of dust explosion; however enrichment with fine dust causes risk of dust explosion.
Reacts with light alloys in the presence of moisture to form hydrogen.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:**
Carbon monoxide and carbon dioxide
Sulphur oxides (SO_x)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:**

- **LD/LC50 values relevant for classification:**

6834-92-0 disodium metasilicate		
Oral	LD50	1280 mg/kg (rat)

- **Primary irritant effect:**
 - **on the skin:** Irritant to skin and mucous membranes.
 - **on the eye:** Irritating effect.
- **Sensitisation:** No sensitising effects known.
- **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:

(Contd. on page 8)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

Irritant

(Contd. of page 7)

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability**
Inorganic product, is not eliminable from water by means of biological cleaning processes.
- **12.3 Bioaccumulative potential** Does not accumulate in organisms.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:**
The product is oxygen-consuming. The declared action may be partly caused by lack of oxygen.
Due to mechanical actions of the product (e.g. agglutinations) damages may occur.
- **Additional ecological information:**
- **General notes:**
This statement was deduced from the properties of the single components.
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Must not reach sewage water or drainage ditch undiluted or unneutralised.
Danger to drinking water if even small quantities leak into the ground.
Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. If the dilution of the use-level pH-value is considerably reduced, the aqueous waste, emptied into drains, is only low water-dangerous.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.
Can be burned with household garbage after consulting with the waste disposal facility operator and the pertinent authorities and adhering to the necessary technical regulations.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

(Contd. on page 9)

Safety Data Sheet
 according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
 OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 8)

SECTION 14: Transport information

- **14.1 UN-Number**
 · DOT, ADR, ADN, IMDG, IATA Not Regulated
- **14.2 UN proper shipping name**
 · DOT, ADR, ADN, IMDG, IATA Not Regulated
- **14.3 Transport hazard class(es)**
 · DOT, ADR, ADN, IMDG, IATA Not Regulated
- **Class** Not Regulated
- **14.4 Packing group**
 · DOT, ADR, IMDG, IATA Not Regulated
- **14.5 Environmental hazards:**
- **Marine pollutant:** No
- **14.6 Special precautions for user** Not applicable.
- **14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code** Not applicable.
- **UN "Model Regulation":** -

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **United States (USA)**
- **SARA**

· Section 355 (extremely hazardous substances):
--

None of the ingredients are listed.

· Section 313 (Specific toxic chemical listings):
--

None of the ingredients are listed.

· TSCA (Toxic Substances Control Act):

All ingredients are listed.

· Proposition 65 (California):

· Chemicals known to cause cancer:

None of the ingredients are listed.

· Chemicals known to cause reproductive toxicity for females:
--

None of the ingredients are listed.

· Chemicals known to cause reproductive toxicity for males:
--

None of the ingredients are listed.

· Chemicals known to cause developmental toxicity:

None of the ingredients are listed.

(Contd. on page 10)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 9)

- **Carcinogenic Categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients are listed.

- **IARC (International Agency for Research on Cancer)**

None of the ingredients are listed.

- **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients are listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients are listed.

- **Canada**

- **Canadian Domestic Substances List (DSL)**

All ingredients are listed.

- **Canadian Ingredient Disclosure list (limit 0.1%)**

None of the ingredients are listed.

- **Canadian Ingredient Disclosure list (limit 1%)**

497-19-8 | sodium carbonate

6834-92-0 | disodium metasilicate

25155-30-0 | sodium dodecylbenzenesulphonate

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients are listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H290 May be corrosive to metals.

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

R22 Harmful if swallowed.

R34 Causes burns.

R36 Irritating to eyes.

R37 Irritating to respiratory system.

R38 Irritating to skin.

R41 Risk of serious damage to eyes.

(Contd. on page 11)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
OSHA GHS

Printing date: 01 August 2019

Revision: 01 August 2019

Trade name: Pink Hi-Active Beads v.7

(Contd. of page 10)

Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
DOT: US Department of Transportation
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
ACGIH: American Conference of Governmental Industrial Hygienists
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
WHMIS: Workplace Hazardous Materials Information System (Canada)
DNEL: Derived No-Effect Level (REACH)
PNEC: Predicted No-Effect Concentration (REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
Met. Corr.1: Corrosive to metals, Hazard Category 1
Acute Tox. 4: Acute toxicity, Hazard Category 4
Skin Corr. 1B: Skin corrosion/irritation, Hazard Category 1B
Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2
Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1
Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2
STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

Sources

SDS Prepared by:
ChemTel Inc.
1305 North Florida Avenue
Tampa, Florida USA 33602-2902
Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573
Website: www.chemtelinc.com