

## T-15

### Super Concentrated Heavy Duty Degreaser

Removes: wax, resin, grease, oil, carbon, dye, soot, scum, gum and ink. All-purpose cleaner for use on any hard surface that is not damaged by water. May be used in manual and pressure washing equipment. Dilutions will vary depending on soil accumulation and the nature of the surface. Hot water will reduce cleaning time and improve performance. Released soil should be removed by rinsing with a clean cloth or sponge. Suggested dilutions are for average soil loads. Use less water or soak longer for heavily soiled surfaces.



#### PRODUCT INFORMATION:

- Formulated to be effective in toughest industrial tasks
- Can be used in pressure washers and industrial scrubbers
- Non-flammable, Biodegradable

pH.....12.0 - 13.5  
Form .....Fluid  
Fragrance .....Pleasant  
Color.....Blue  
Packaged .....4/1 gl Case, 5 gl Pail, 55 gl Drum

#### DIRECTIONS FOR USE:

All-purpose cleaner for use on any hard surface that is not damaged by water. May be used in manual and pressure washing equipment. Dilutions will vary depending on soil accumulation and the nature of the surface. Hot water will reduce cleaning time and improve performance. Released soil should be removed by rinsing with a clean cloth or sponge. Suggested dilutions are for average soil loads. Use less water or soak longer for heavily soiled surfaces. **FOR WAX STRIPPING (MANUAL):** For Asphalt, Tile, Rubber, Vinyl, Terrazzo and all other types of floors dilute 1:30. **FOR METAL INTERLOCK FINISHES:** Follow instructions for wax stripping. Add 1 cup of household ammonia to each gallon of water. You will obtain better results if the solution is allowed to remain on the floor to be stripped for 5 minutes and then agitate with a stiff brush or scrubber. Rinse with warm water. **FOR CLEANING FLOORS:** For Concrete, Ceramic Tile, Terrazzo, Magnesite, Vinyl and Rubber dilute 1:100; For Heavy Soil and Grease dilute 1:40. **FOR KITCHEN CLEANING:** For Ovens and Deep Fat Fryers dilute 1:10; For Flues, Canopies and Ducts over Ovens dilute 1:20; For Greasy Floor and Wooden Mats dilute 1:30; For Walls and Refrigerators dilute 1:60; For Lighting Fixtures dilute 1:100. **FOR AIRPLANES, BUSES, AND TRUCKS:** Dilute 1:15. **FOR PRINTERS:** For Presses, Walls, and Floors dilute 1:15; For Heavy Ink Deposits dilute 1:10. **FOR AUTOMATIC SCRUBBING MACHINES:** For light Cleaning dilute 1:200; For Heavy Soil and Grease dilute 1:100; For Wax Stripping dilute 1:40. Cleaner will work better in hot water if solution is allowed to stand on the floor for 5 minutes. Rinse with clear water. **FOR SCHOOLS:** For Gymnasiums dilute 1:15; For Lockers and Steel Files dilute 1:60; For Showers and Swimming Pools dilute 1:10. **AUTOMOBILES:** For Convertible Tops dilute 1:40; For White Wall Tires and Degreasing Engines dilute 1:10. **EQUIPMENT OF ALL KINDS:** Dilute 1:20; For Windows, Glass and Stainless Steel dilute 1:40; For Grease and Heavy Soil on Stainless Steel dilute 1:20.

Meets USDA guidelines for use in federally inspected meat and poultry processing plants.

#### IMPORTANT SAFETY INFORMATION:



##### **DANGER**

Causes severe skin burns and eye damage.

Do not breathe vapors. Wash hands thoroughly after handling. Wear protective gloves, protective clothing, eye protection and face protection.

**FIRST AID: IF ON SKIN (or hair):** Remove immediately all contaminated clothing. Rinse skin with water. Wash contaminated clothing before reuse. **IF IN EYES:** Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. **IF INHALED:** Remove victim to fresh air and keep at rest in a position comfortable for breathing. **IF SWALLOWED:** rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTER or physician.

Emergency Response Number ChemTel Inc. 1-800-255-3924

**SOLUTIONS FOR A CLEANER WORLD™**



**THEOCHEM LABORATORIES, INC.** 7373 Rowlett Park Drive • Tampa, Florida 33610 • (813) 237-6463 • [www.theochem.com](http://www.theochem.com)



100478-0517v1