

### Features

- Wide coverage spray produces an encompassing spray for everyday use.
- 1.5 gpm (5.7 lpm) maximum flow rate handshower allows you to save water without sacrificing performance or coverage.
- Variable-flow lever lets you adjust from 1.5 gpm (5.7 lpm) down to 0.5 gpm (1.9 lpm) water pause for greater conservation during your shower routine.
- Sprayface resists hard water buildup and is easy to clean.
- Magnetic docking connection allows for handshower height adjustment of 2" (51 mm) and spray angle tilt of 24-58°.

### Material

- Premium metal construction for durability and reliability.
- KOHLER finishes resist corrosion and tarnishing.
- Hose is a durable, flexible polymer blend with soft-touch finish for a hassle-free drape.

### Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray.

### Installation

- Wall-mount.
- For use in shower-only installations.

### Water Conservation & Rebates

- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System.

### Recommended Products/Accessories

K-23723 Faucet cleaner

### Included Components

Additional Components:

20998  
21049  
21051



### Codes/Standards




ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)


### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black



### Technical Information

All product dimensions are nominal.

#### Handshower:

Rated maximum flow: 1.5 gal/min (5.7 l/min)  
Pressure: 45 psi (3.1 bar)