

This safety data sheet was created pursuant to the requirements of: US OSHA Hazard Communication Standard (29 CFR 1910.1200) and Canada WHMIS 2015 which includes the amended Hazardous Products Act (HPA) and the Hazardous Products Regulation (HPR)

Issuing Date 14-Oct-2019

Revision Date 14-Oct-2019

Revision Number 1

1. Identification

Product identifier

Product Name High Speed 100 Spindle Oil Bearing Lubricant

Other means of identification

Product Code(s) 270

Other information Blend Revision ID 3046

Recommended use of the chemical and restrictions on use

Recommended use Lubricant

Restrictions on use No information available.

Details of the supplier of the safety data sheet

Supplier Address

U.S. Lubricants, a Division of U.S. Venture Inc.
425 Better Way
Appleton, WI 54915
800-490-4900

Emergency telephone number

Emergency Telephone 800-490-4900
Chemtrec 1-800-424-9300 (Account# 705487)

2. Hazard(s) identification

Classification

Not classified.

Label elements

Hazard statements

Not classified.

Other information

No information available.

3. Composition/information on ingredients

Substance

Not applicable.

Mixture

Chemical name	CAS No	Weight-%	Hazardous Material Information Review Act registry number (HMIRA registry #)	Date HMIRA filed and date exemption granted (if applicable)
2,6-Di-tert-butylphenol	128-39-2	<1	-	-
Mineral oil*	-	<1	-	-

Chemical Additions

* The mineral oil contained in this material may be described by one or more of the following CAS Nos.: 64742-54-7, 64742-65-0, 64742-55-8, and 64742-56-9.

4. First-aid measures

Description of first aid measures

Inhalation	Remove to fresh air.
Eye contact	Rinse thoroughly with plenty of water, also under the eyelids. Get medical attention if symptoms occur.
Skin contact	Wash skin with soap and water. Get medical attention if symptoms occur. Wash contaminated clothing before reuse.
Ingestion	If large quantities of this material are swallowed, call a physician immediately.

Most important symptoms and effects, both acute and delayed

Symptoms None known.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. Fire-fighting measures

Suitable Extinguishing Media	Dry chemical, CO2, water spray or regular foam.
Unsuitable extinguishing media	Water spray jet.
Specific hazards arising from the chemical	Thermal decomposition can lead to release of irritating gases and vapors.
Hazardous combustion products	Oxides of sulfur. Aldehydes. Ketones and their derivatives. Carbon monoxide. Organic compounds.
Explosion data	
Sensitivity to mechanical impact	None.
Sensitivity to static discharge	None.

Special protective equipment for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep people away from and upwind of spill/leak. Extremely slippery when spilled. Use personal protective equipment as required. See section 8 for more information. Avoid contact with skin, eyes or clothing. Deny entry to unauthorized and unprotected personnel.

Methods and material for containment and cleaning up

Methods for containment Dike far ahead of liquid spill for later disposal.

Methods for cleaning up Take up with sand or other noncombustible absorbent material and place into containers for later disposal.

7. Handling and storage

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Ensure adequate ventilation. Use personal protection equipment. Avoid contact with skin, eyes or clothing. Avoid breathing vapors or mists. Wash thoroughly after handling. Do not eat, drink or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a cool, well-ventilated place.

8. Exposure controls/personal protection

Control parameters

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Mineral oil* -	TWA: 5 mg/m ³ (inhalable fraction)	PEL: 5 mg/m ³ (mist)	REL: 5 mg/m ³ (mist) STEL: 10 mg/m ³ (mist)

Appropriate engineering controls

Engineering controls Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection	Goggles.
Hand protection	Impervious gloves. Protective gloves.
Skin and body protection	Wear suitable protective clothing.
Respiratory protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice. Wash thoroughly after handling. Avoid breathing vapors or mists. Avoid contact with skin, eyes or clothing. Take off contaminated clothing and wash before reuse.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance

Physical state	Liquid
Color	Light amber
Odor	Mild Petroleum
Odor threshold	No information available

Property

Values

Remarks • Method

pH	No data available	None known
Melting point / freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flash point	215.6 °C / 420.1 °F	
Evaporation rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Relative density	0.854 (7.11 lb/gal)	
Water solubility	Insoluble in water	
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	21 - 24 cSt	@ 40 °C
Dynamic viscosity	No data available	None known

Other information

Explosive properties	No information available.
Oxidizing properties	No information available.
Softening point	No information available
Molecular weight	No information available
VOC Content (%)	.? Negligible
Liquid Density	No information available
Bulk density	No information available

10. Stability and reactivity

Reactivity	None under normal use conditions.
-------------------	-----------------------------------

Chemical stability	Stable under normal conditions.
Possibility of hazardous reactions	None under normal processing.
Conditions to avoid	Extremes of temperature and direct sunlight.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	None known based on information supplied.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Specific test data for the substance or mixture is not available.
Eye contact	Specific test data for the substance or mixture is not available. Contact with eyes may cause irritation.
Skin contact	Specific test data for the substance or mixture is not available.
Ingestion	Specific test data for the substance or mixture is not available.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms	None known.
-----------------	-------------

Acute toxicity

Numerical measures of toxicity
No information available

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
2,6-Di-tert-butylphenol	> 5000 mg/kg (Rat)	> 10 g/kg (Rabbit)	

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	No information available.
Serious eye damage/eye irritation	No information available.
Respiratory or skin sensitization	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	The classification listed below for the petroleum distillates in this product pertains to those that contain more than 3% DMSO extract as measured by IP 346. The petroleum distillates in this product do not meet that criteria to be classified as carcinogens.

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Mineral oil*	A2	Group 1	Known	X
-				

Legend

ACGIH (American Conference of Governmental Industrial Hygienists)

A2 - Suspected Human Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Aspiration hazard	No information available.

12. Ecological information

Ecotoxicity The environmental impact of this product has not been fully investigated.

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
2,6-Di-tert-butylphenol 128-39-2	-	-	-	EC50: =0.45mg/L (48h, Daphnia magna)
Mineral oil* -	-	LC 50: > 100 mg/L (4d, Fathead Minnow)	-	EC 50: > 10,000 mg/L (2d, Water flea (Daphnia magna)) EC 50: > 10 mg/L (21d, Water flea (Daphnia magna)) NOEC: > 10 mg/L (21d, Water flea (Daphnia magna))

Persistence and degradability	No information available.
Bioaccumulation	No information available.
Mobility in soil	No information available.
Other adverse effects	No information available.

13. Disposal considerations**Waste treatment methods**

Waste from residues/unused products	Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.
Contaminated packaging	Do not reuse empty containers.

14. Transport information

<u>DOT</u>	Not regulated
<u>TDG</u>	Not regulated
<u>MEX</u>	Not regulated
<u>IATA</u>	Not regulated
<u>IMDG</u>	Not regulated

15. Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

International Regulations

The Montreal Protocol on Substances that Deplete the Ozone Layer Not applicable

The Stockholm Convention on Persistent Organic Pollutants Not applicable

The Rotterdam Convention Not applicable

International Inventories

TSCA Contact supplier for inventory compliance status.
DSL/NDSL Contact supplier for inventory compliance status.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications. Under the amended regulations at 40 CFR 370, EPCRA 311/312 Tier II reporting for the 2017 calendar year will need to be consistent with updated hazard classifications.

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

US State Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
2-Ethylhexanol 104-76-7	-	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

16. Other information

NFPA	Health hazards 1	Flammability 1	Instability 0	Physical and chemical properties -
HMIS	Health hazards 1	Flammability 1	Physical hazards 0	Personal protection X

Key or legend to abbreviations and acronyms used in the safety data sheetLegend Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

Key literature references and sources for data used to compile the SDS

U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 EPA (Environmental Protection Agency)
 Acute Exposure Guideline Level(s) (AEGl(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 Japan GHS Classification
 Australia National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)
 National Library of Medicine's ChemID Plus (NLM CIP)
 National Toxicology Program (NTP)
 New Zealand's Chemical Classification and Information Database (CCID)
 Organization for Economic Co-operation and Development Environment, Health, and Safety Publications
 Organization for Economic Co-operation and Development High Production Volume Chemicals Program
 Organization for Economic Co-operation and Development Screening Information Data Set
 RTECS (Registry of Toxic Effects of Chemical Substances)
 World Health Organization

Issuing Date	14-Oct-2019
Revision Date	14-Oct-2019
Revision Note	Initial Release.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet