

# SAFETY DATA SHEET

National Premium Full Synthetic 0W-16, 0W-20, 5W-20, 5W-30, 10W-30

## Section 1. Identification

**GHS product identifier** : S149  
**Product code** : 07-1706287, 07-130020, 07-195520, 07-195530, 07-195130  
**Other means of identification** : 0W-16, 0W-20, 5W-20, 5W-30, 10W-30  
**Product type** : Liquid.

### Relevant identified uses of the substance or mixture and uses advised against

**Identified uses** :

**Supplier's details** : Pinnacle Oil Holdings, LLC  
8175-B Allison Ave.  
Indianapolis, IN 46268

**Manufactured by** : Pinnacle Oil Holdings, LLC  
8175-B Allison Ave.  
Indianapolis, IN 46268  
Tel: 317-875-9465  
Fax: 317-875-0889  
www.pinnacleoil.com  
Email: SDS@pinnoil.com

**Emergency telephone number (with hours of operation)** : CHEMTREC, U.S.: 1-800-424-9300 International: +1-703-527-3887 (24/7)

## Section 2. Hazards identification

**OSHA/HCS status** : While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this SDS contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and available for employees and other users of this product.

**Classification of the substance or mixture** : Not classified.

### GHS label elements

**Signal word** : No signal word.

**Hazard statements** : No known significant effects or critical hazards.

### Precautionary statements

**Prevention** : Not applicable.

**Response** : Not applicable.

**Storage** : Not applicable.

**Disposal** : Not applicable.

**Hazards not otherwise classified** : None known.



## Section 3. Composition/information on ingredients

**Substance/mixture** : Mixture  
**Other means of identification** :

Ingredient name	%	CAS number
Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based	80 - 100	72623-87-1
Distillates (petroleum), hydrotreated heavy paraffinic	15 - 40	64742-54-7
Paraffin oils (petroleum), catalytic dewaxed light	3 - 7	64742-71-8

**United States:** The exact percentage (concentration) in the composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

**Canada:** The exact percentage (concentration) in the composition has been withheld as a trade secret in accordance with the amended HPR as of April 2018.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

## Section 4. First aid measures

### Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.
- Skin contact** : Flush contaminated skin with plenty of water. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

### Most important symptoms/effects, acute and delayed

#### Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

#### Over-exposure signs/symptoms

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

### Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

See toxicological information (Section 11)



## Section 5. Fire-fighting measures

### Extinguishing media

- Suitable extinguishing media** : In case of fire, use foam, dry chemical or carbon dioxide.
- Unsuitable extinguishing media** : Do not use high volume water jet as an extinguisher, as this may spread the fire.
- Specific hazards arising from the chemical** : No specific fire or explosion hazard.
- Hazardous thermal decomposition products** : Carbon oxides
- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

## Section 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### Methods and materials for containment and cleaning up

- Spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

## Section 7. Handling and storage

### Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8).
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.



## Section 7. Handling and storage

**Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

## Section 8. Exposure controls/personal protection

### Control parameters

#### United States

##### Occupational exposure limits

Ingredient name	Exposure limits
Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based	<b>NIOSH REL (United States, 10/2016).</b> TWA: 5 mg/m <sup>3</sup> 10 hours. Form: Mist STEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist
Distillates (petroleum), hydrotreated heavy paraffinic	<b>OSHA PEL (United States, 5/2018).</b> TWA: 5 mg/m <sup>3</sup> 8 hours. <b>ACGIH TLV (United States, 3/2018).</b> TWA: 5 mg/m <sup>3</sup> 8 hours. Form: Inhalable fraction <b>NIOSH REL (United States, 10/2016).</b> TWA: 5 mg/m <sup>3</sup> 10 hours. Form: Mist STEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist
Paraffin oils (petroleum), catalytic dewaxed light	<b>OSHA PEL (United States, 5/2018).</b> TWA: 5 mg/m <sup>3</sup> 8 hours. <b>ACGIH TLV (United States, 3/2018).</b> TWA: 5 mg/m <sup>3</sup> 8 hours. Form: Inhalable fraction <b>NIOSH REL (United States, 10/2016).</b> TWA: 5 mg/m <sup>3</sup> 10 hours. Form: Mist STEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist

#### Canada

##### Occupational exposure limits

Ingredient name	Exposure limits
Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based	<b>CA Alberta Provincial (Canada, 6/2018).</b> 8 hrs OEL: 5 mg/m <sup>3</sup> 8 hours. Form: Mist 15 min OEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist <b>CA Quebec Provincial (Canada, 1/2014).</b> TWAEV: 5 mg/m <sup>3</sup> 8 hours. Form: mist STEV: 10 mg/m <sup>3</sup> 15 minutes. Form: mist
Distillates (petroleum), hydrotreated heavy paraffinic	<b>CA Alberta Provincial (Canada, 6/2018).</b> 8 hrs OEL: 5 mg/m <sup>3</sup> 8 hours. Form: Mist 15 min OEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist <b>CA Quebec Provincial (Canada, 1/2014).</b> TWAEV: 5 mg/m <sup>3</sup> 8 hours. Form: Mist STEV: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist
Paraffin oils (petroleum), catalytic dewaxed light	<b>CA Alberta Provincial (Canada, 6/2018).</b> 8 hrs OEL: 5 mg/m <sup>3</sup> 8 hours. Form: Mist 15 min OEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist <b>CA Quebec Provincial (Canada, 1/2014).</b> TWAEV: 5 mg/m <sup>3</sup> 8 hours. Form: Mist STEV: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist

**Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.

### Individual protection measures



## Section 8. Exposure controls/personal protection

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

## Section 9. Physical and chemical properties

### Appearance

- Physical state** : Liquid.
- Color** : Brown.
- Odor** : Petroleum.
- Odor threshold** : Not available.
- pH** : Not available.
- Melting point** : Not available.
- Boiling point** : Not available.
- Flash point, COC** : >180°C (>356°F)
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Not available.
- Lower and upper explosive (flammable) limits** : Not available.
- Vapor pressure** : Not available.
- Vapor density** : Not available.
- Specific gravity @ 60F** : 0.85 to 0.9
- Solubility** : Not available.
- Partition coefficient: n-octanol/water** : Not available.
- Auto-ignition temperature** : Not available.
- Decomposition temperature** : Not available.
- Kinematic Viscosity at 40°C** : >34 cSt
- Flow time (ISO 2431)** : Not available.

## Section 10. Stability and reactivity

- Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- Chemical stability** : The product is stable.
- Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.
- Conditions to avoid** : No specific data.
- Incompatible materials** : Reactive or incompatible with the following materials: oxidizing materials.
- Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## Section 11. Toxicological information

### Information on toxicological effects

#### Acute toxicity

There is no data available.

#### Irritation/Corrosion

There is no data available.

#### Sensitization

There is no data available.

#### Mutagenicity

There is no data available.

#### Carcinogenicity

There is no data available.

#### Reproductive toxicity

There is no data available.

#### Teratogenicity

There is no data available.

#### Specific target organ toxicity (single exposure)

There is no data available.

#### Specific target organ toxicity (repeated exposure)

There is no data available.

#### Aspiration hazard

Name	Result
Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based Paraffin oils (petroleum), catalytic dewaxed light	ASPIRATION HAZARD - Category 1 ASPIRATION HAZARD - Category 1

- Information on the likely routes of exposure** : Dermal contact. Eye contact. Inhalation. Ingestion.

### Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.

## Section 11. Toxicological information

**Ingestion** : No known significant effects or critical hazards.

### Symptoms related to the physical, chemical and toxicological characteristics

**Eye contact** : No known significant effects or critical hazards.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

**Ingestion** : No known significant effects or critical hazards.

### Delayed and immediate effects and also chronic effects from short and long term exposure

#### Short term exposure

**Potential immediate effects** : No known significant effects or critical hazards.

**Potential delayed effects** : No known significant effects or critical hazards.

#### Long term exposure

**Potential immediate effects** : No known significant effects or critical hazards.

**Potential delayed effects** : No known significant effects or critical hazards.

#### Potential chronic health effects

**General** : No known significant effects or critical hazards.

**Carcinogenicity** : No known significant effects or critical hazards.

**Mutagenicity** : No known significant effects or critical hazards.

**Teratogenicity** : No known significant effects or critical hazards.

**Developmental effects** : No known significant effects or critical hazards.

**Fertility effects** : No known significant effects or critical hazards.

### Numerical measures of toxicity

#### Acute toxicity estimates

There is no data available.

## Section 12. Ecological information

### Toxicity

There is no data available.

### Persistence and degradability

There is no data available.

### Bioaccumulative potential

There is no data available.

### Mobility in soil

**Soil/water partition coefficient ( $K_{oc}$ )** : Not available.

**Other adverse effects** : No known significant effects or critical hazards.

## Section 13. Disposal considerations

**Disposal methods** : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

## Section 14. Transport information

	DOT Classification	TDG Classification	IMDG	IATA
UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
UN proper shipping name	-	-	-	-
Transport hazard class(es)	-	-	-	-
Packing group	-	-	-	-
Environmental hazards	No.	No.	No.	No.

**AERG** : Not applicable.

**Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

## Section 15. Regulatory information

**U.S. Federal regulations** : **United States inventory (TSCA 8b):** Not determined.  
**Clean Water Act (CWA) 307:** Zinc O,O',O'-tetrakis(1,3-dimethylbutyl) bis (phosphorodithioate); Zinc bis[O,O-bis(2-ethylhexyl)] bis(dithiophosphate); Naphthalene; Toluene; Benzene; Ethylbenzene  
**Clean Water Act (CWA) 311:** Naphthalene; Toluene; Benzene; Ethylbenzene; Propylene oxide

**Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)** : Listed

**Clean Air Act Section 602 Class I Substances** : Not listed

**Clean Air Act Section 602 Class II Substances** : Not listed

**DEA List I Chemicals (Precursor Chemicals)** : Not listed





## Section 15. Regulatory information

**DEA List II Chemicals (Essential Chemicals)** : Not listed

### SARA 302/304

#### Composition/information on ingredients

Name	EHS	SARA 302 TPQ		SARA 304 RQ	
		(lbs)	(gallons)	(lbs)	(gallons)
Propylene oxide	Yes.	10000	1444.3	100	14.4
Ethylene oxide	Yes.	1000	-	10	-

**SARA 304 RQ** : 1338688085.7 lbs / 607764390.9 kg [183490704.3 gal / 694587875.3 L]

### SARA 311/312

**Classification** : Not applicable.

#### Composition/information on ingredients

Name	Classification
Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based	ASPIRATION HAZARD - Category 1
Paraffin oils (petroleum), catalytic dewaxed light	ASPIRATION HAZARD - Category 1

### SARA 313

There is no data available.

### State regulations

#### Massachusetts

: The following components are listed: Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based; Distillates (petroleum), hydrotreated heavy paraffinic; Paraffin oils (petroleum), catalytic dewaxed light

#### New York

: None of the components are listed.

#### New Jersey

: The following components are listed: Lubricating oils (petroleum), C20-50, hydrotreated neutral oil-based

#### Pennsylvania

: None of the components are listed.

#### California Prop. 65

**WARNING:** This product can expose you to chemicals including Benzene and Ethylene oxide, which are known to the State of California to cause cancer and birth defects or other reproductive harm. This product can expose you to chemicals including Naphthalene, Ethylbenzene, Propylene oxide and 1,4-Dioxane, which are known to the State of California to cause cancer, and Toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

Ingredient name	No significant risk level	Maximum acceptable dosage level
Naphthalene	Yes.	-
Toluene	-	Yes.
Benzene	Yes.	Yes.
Ethylbenzene	Yes.	-
Propylene oxide	-	-
Ethylene oxide	Yes.	Yes.
1,4-Dioxane	Yes.	-

### Canadian lists

#### Canada inventory (DSL NDSL)

: Not determined.

#### Canadian NPRI

: None of the components are listed.

#### CEPA Toxic substances

: None of the components are listed.



## Section 16. Other information

### National Fire Protection Association (U.S.A.)

**Health :** 0    **Flammability :** 1    **Instability :** 0

Reprinted with permission from NFPA 704-2001, Identification of the Hazards of Materials for Emergency Response Copyright ©1997, National Fire Protection Association, Quincy, MA 02269. This reprinted material is not the complete and official position of the National Fire Protection Association, on the referenced subject which is represented only by the standard in its entirety.

Copyright ©2001, National Fire Protection Association, Quincy, MA 02269. This warning system is intended to be interpreted and applied only by properly trained individuals to identify fire, health and reactivity hazards of chemicals. The user is referred to certain limited number of chemicals with recommended classifications in NFPA 49 and NFPA 325, which would be used as a guideline only. Whether the chemicals are classified by NFPA or not, anyone using the 704 systems to classify chemicals does so at their own risk.

#### NFPA Hazard Ratings

4 = extreme

3 = high

2 = moderate

1 = slight

0 = insignificant

N = no rating for powders

### Procedure used to derive the classification

Classification	Justification
Not classified.	

### History

**Date of issue mm/dd/yyyy** : 05/15/2020

**Date of previous issue** : 04/15/2020

**Version** : 1.1

**Prepared by** : KMK Regulatory Services Inc.

### Key to abbreviations

: ATE = Acute Toxicity Estimate

BCF = Bioconcentration Factor

GHS = Globally Harmonized System of Classification and Labelling of Chemicals

IATA = International Air Transport Association

IBC = Intermediate Bulk Container

IMDG = International Maritime Dangerous Goods

LogPow = logarithm of the octanol/water partition coefficient

MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)

UN = United Nations

**Internal code** : 231-154

### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

