

This safety data sheet was created pursuant to the requirements of:
US OSHA Hazard Communication Standard (29 CFR 1910.1200) and Canada WHMIS
2015 which includes the amended Hazardous Products Act (HPA) and the Hazardous
Products Regulation (HPR)

Revision date 11/30/2022

Revision Number 1

1. Identification

Product identifier

Product Name Thrive 0W20 Dexos 1 Gen 3

Other means of identification

Product Code(s) 200-005

Synonyms None

Other information Blend Revision ID 4168

Recommended use of the chemical and restrictions on use

Recommended use Lubricant

Restrictions on use No information available

Details of the supplier of the safety data sheet

Supplier Address

U.S. Lubricants, a Division of U.S. Venture Inc.
425 Better Way
Appleton, WI 54915
800-490-4900

Emergency telephone number

Emergency Telephone 800-490-4900 Chemtrec 1-800-424-9300 (Account# 705487)

2. Hazard(s) identification

Classification

Acute toxicity - Inhalation (Dusts/Mists)	Category 4
---	------------

Appearance No information available

Physical state Liquid

Odor Mild Petroleum

Label elements

Warning

Hazard statements

Harmful if inhaled

**Precautionary Statements - Prevention**

Avoid breathing dust, fume, gas, mist, vapors and spray

Use only outdoors or in a well-ventilated area

Precautionary Statements - Response**Inhalation**

IF INHALED: Remove person to fresh air and keep comfortable for breathing

Call a doctor if you feel unwell

Other information

May be harmful in contact with skin.

3. Composition/information on ingredients

Substance

Not applicable.

Mixture

Chemical name	CAS No	Weight-%	Hazardous Material Information Review Act registry number (HMIRA registry #)	Date HMIRA filed and date exemption granted (if applicable)
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based	72623-87-1	80-90	-	-

4. First-aid measures

Description of first aid measures**General advice**

Show this safety data sheet to the doctor in attendance.

Inhalation

Remove to fresh air. If symptoms persist, call a physician. If breathing has stopped, give artificial respiration. Get medical attention immediately.

Eye contact

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Skin contact

Wash skin with soap and water.

Ingestion

Do NOT induce vomiting. Rinse mouth. Never give anything by mouth to an unconscious person. Get medical attention.

Self-protection of the first aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Avoid breathing vapors or mists. Use personal protective equipment as required. See section 8 for more information.

Most important symptoms and effects, both acute and delayed

Symptoms Coughing and/ or wheezing. Difficulty in breathing.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. Fire-fighting measures

Suitable Extinguishing Media Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Large Fire CAUTION: Use of water spray when fighting fire may be inefficient.

Unsuitable extinguishing media Water spray jet.

Specific hazards arising from the chemical No information available.

Hazardous combustion products Oxides of sulfur. Aldehydes. Ketones and their derivatives. Carbon monoxide. Organic compounds.

Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

Special protective equipment and precautions for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Deny entry to unauthorized and unprotected personnel. Ensure adequate ventilation. Avoid breathing vapors or mists. Use personal protective equipment as required.

Other information Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. Handling and storage

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid breathing vapors or mists. Ensure adequate ventilation. In case of insufficient ventilation, wear suitable respiratory equipment. Do not eat, drink or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Keep out of the reach of children.

8. Exposure controls/personal protection

Control parameters

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL	NIOSH	
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	TWA: 5 mg/m ³ inhalable particulate matter excluding metal working fluids, highly & severely refined	TWA: 5 mg/m ³ (vacated) TWA: 5 mg/m ³	IDLH: 2500 mg/m ³ TWA: 5 mg/m ³ STEL: 10 mg/m ³	
Chemical name	Alberta	British Columbia	Ontario	Quebec
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	TWA: 5 mg/m ³ STEL: 10 mg/m ³	TWA: 0.2 mg/m ³ TWA: 1 mg/m ³	TWA: 5 mg/m ³ TWA:	TWA: 5 mg/m ³ STEL: 10 mg/m ³

Appropriate engineering controls

Engineering controls Showers
 Eyewash stations
 Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection No special protective equipment required.

Hand protection No special protective equipment required.

Skin and body protection No special protective equipment required.

Respiratory protection No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

General hygiene considerations Do not eat, drink or smoke when using this product.

9. Physical and chemical properties

Information on basic physical and chemical properties

Physical state Liquid
Appearance No information available
Color amber
Odor Mild Petroleum
Odor threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No data available	Neutral
Melting point / freezing point	No data available	None known
Initial boiling point and boiling range	No data available	None known
Flash point	216 °C / 420.8 °F	
Evaporation rate	No data available	None known
Flammability	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	

Vapor pressure	No data available	None known
Relative vapor density	No data available	None known
Relative density	0.85 (7.05 lb/gal)	
Water solubility	Insoluble in water	
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	8 - 9 cSt	@ 100 °C
Dynamic viscosity	No data available	None known

Other information

Explosive properties	No information available
Oxidizing properties	No information available
Softening point	No information available
Molecular weight	No information available
VOC Content (%)	No information available
Liquid Density	No information available
Bulk density	No information available

10. Stability and reactivity

Reactivity	No information available.
Chemical stability	Stable under normal conditions.
Possibility of hazardous reactions	None under normal processing.
Conditions to avoid	Excessive heat.
Incompatible materials	None known based on information supplied.
Hazardous decomposition products	None known based on information supplied.

11. Toxicological information**Information on likely routes of exposure****Product Information**

Inhalation	Specific test data for the substance or mixture is not available. Harmful by inhalation. (based on components).
Eye contact	Specific test data for the substance or mixture is not available.
Skin contact	May be harmful in contact with skin.
Ingestion	Specific test data for the substance or mixture is not available.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms	Coughing and/ or wheezing.
----------	----------------------------

Acute toxicity**Numerical measures of toxicity**

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	5,555.60 mg/kg
ATEmix (dermal)	2,222.20 mg/kg
ATEmix (inhalation-dust/mist)	2.42 mg/l

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	= 2.18 mg/L (Rat) 4 h

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation No information available.

Serious eye damage/eye irritation No information available.

Respiratory or skin sensitization No information available.

Germ cell mutagenicity No information available.

Carcinogenicity The classification listed below for the petroleum distillates in this product pertains to those that contain more than 3% DMSO extract as measured by IP 346. The petroleum distillates in this product do not meet that criteria to be classified as carcinogens.

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	A2	-	-	-

Legend**ACGIH (American Conference of Governmental Industrial Hygienists)**

A2 - Suspected Human Carcinogen

Reproductive toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Target organ effects Respiratory system, Eyes, Skin.

Aspiration hazard No information available.

12. Ecological information**Ecotoxicity**

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	-	LC50: >5000mg/L (96h, Oncorhynchus mykiss)	-	EC50: >1000mg/L (48h, Daphnia magna)

Persistence and degradability No information available.

Bioaccumulation	There is no data for this product.
Mobility in soil	No information available.
Other adverse effects	No information available.

13. Disposal considerations

Disposal methods

Waste from residues/unused products	Dispose of waste in accordance with environmental legislation. Dispose of in accordance with local regulations.
Contaminated packaging	Do not reuse empty containers.

14. Transport information

<u>DOT</u>	Not regulated
------------	---------------

15. Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

International Regulations

The Montreal Protocol on Substances that Deplete the Ozone Layer Not applicable

The Stockholm Convention on Persistent Organic Pollutants Not applicable

The Rotterdam Convention Not applicable

International Inventories

TSCA	Contact supplier for inventory compliance status.
DSL/NDSL	Contact supplier for inventory compliance status.
EINECS/ELINCS	Contact supplier for inventory compliance status.
ENCS	Contact supplier for inventory compliance status.
IECSC	Contact supplier for inventory compliance status.
KECL	Contact supplier for inventory compliance status.
PICCS	Contact supplier for inventory compliance status.
AIIC	Contact supplier for inventory compliance status.
NZIoC	Contact supplier for inventory compliance status.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AIIC - Australian Inventory of Industrial Chemicals
NZIoC - New Zealand Inventory of Chemicals

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

16. Other information

NFPA	Health hazards 2	Flammability 1	Instability 0	Special hazards -
HMIS	Health hazards 2	Flammability 1	Physical hazards 0	Personal protection X

Key or legend to abbreviations and acronyms used in the safety data sheet

Legend Section 8: Exposure controls/personal protection

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)
 U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 EPA (Environmental Protection Agency)

Acute Exposure Guideline Level(s) (AEGl(s))
U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
U.S. Environmental Protection Agency High Production Volume Chemicals
Food Research Journal
Hazardous Substance Database
International Uniform Chemical Information Database (IUCLID)
National Institute of Technology and Evaluation (NITE)
Australia National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
NIOSH (National Institute for Occupational Safety and Health)
National Library of Medicine's ChemID Plus (NLM CIP)
National Library of Medicine's PubMed database (NLM PUBMED)
National Toxicology Program (NTP)
New Zealand's Chemical Classification and Information Database (CCID)
Organization for Economic Co-operation and Development Environment, Health, and Safety Publications
Organization for Economic Co-operation and Development High Production Volume Chemicals Program
Organization for Economic Co-operation and Development Screening Information Data Set
World Health Organization

Revision date 11/30/2022

Revision Note No information available.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet