



SAFETY DATA SHEET

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200 and WHMIS 2015, in compliance with the Hazardous Product Act (HPA, as amended) and the requirements of the Hazardous Product Regulations (HPR).

1. Identification

Product identifier

Product name Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

Product number 541, 542, 543

Recommended use of the chemical and restrictions on use

Application Lubricating fluid.

Uses advised against Avoid the formation of mists.

Details of the supplier of the safety data sheet

Supplier U.S. Lubricants, A Division of U.S. Venture, Inc.
425 Better Way
Appleton, WI 54915

Emergency telephone number CHEMTREC: Within USA and Canada: 1-800-424-9300

Emergency telephone Outside the USA and Canada: +1 703-741-5970
(collect calls accepted) 24/7

2. Hazard(s) identification

Classification of the substance or mixture

OSHA/WHMIS Regulatory Status This Product is not Hazardous under the OSHA Hazard Communication Standard and according to the hazard criteria of the Hazardous Product Regulations.

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

Label elements

Hazard statements NC Not Classified

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

Mixtures

Composition comments No classified ingredients, or those having occupational exposure limits, present above the levels of disclosure.

4. First-aid measures

Description of first aid measures

General information Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.

Inhalation Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.

Ingestion Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.

Skin Contact Wash skin thoroughly with soap and water.

Eye contact Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.

Protection of first aiders First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation.

Skin contact Prolonged contact may cause dryness of the skin.

Eye contact May cause temporary eye irritation.

Indication of immediate medical attention and special treatment needed

Notes for the doctor Treat symptomatically.

Specific treatments No special treatment required.

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards Containers can burst or explode when heated, due to excessive pressure build-up. Contains Hydrocarbons. The product is immiscible with water and will spread on the water surface.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapors and protect men stopping the leak.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves, that provides a basic level of protection during chemical incidents is defined by the Canada Occupational Health and Safety Regulations, by provincial guidelines on occupational health and safety or by NFPA standards if applicable.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions	No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Use protective equipment appropriate for surrounding materials.
-----------------------------	---

Environmental precautions

Environmental precautions	Avoid discharge to the aquatic environment.
----------------------------------	---

Methods and material for containment and cleaning up

Methods for cleaning up	Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Reuse or recycle products wherever possible. Absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.
--------------------------------	--

Reference to other sections	For personal protection, see Section 8. For waste disposal, see Section 13.
------------------------------------	---

7. Handling and storage

Precautions for safe handling

Usage precautions	Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimize spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Avoid contact with used product. Do not reuse empty containers.
--------------------------	---

Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.
---	---

Conditions for safe storage, including any incompatibilities

Storage precautions	Store away from incompatible materials (see Section 10). Keep container tightly closed, in a cool, well ventilated place. Protect containers from damage.
----------------------------	---

Storage class	Chemical storage.
----------------------	-------------------

Specific end uses(s)

Specific end use(s)	The identified uses for this product are detailed in Section 1.
----------------------------	---

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

8. Exposure controls/Personal protection

Control parameters

Occupational exposure limits

Comments The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

Under conditions which may generate mists, the following exposure limits are recommended:

Long-term exposure limit (8-hour TWA): 5 mg/m³

Short-term exposure limit (15-minute): 10 mg/m³

Exposure controls

Appropriate engineering controls Provide adequate ventilation. Good general ventilation should be adequate to control worker exposure to airborne contaminants.

Eye/face protection Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with OSHA 1910.133 and/or the Canadian regulation on health and safety at work, SOR/86-304, Part XII (12.6), and any relevant provincial regulation relating to health and safety at work. The following protection should be worn: Chemical splash goggles.

Hand protection Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and/or the Canadian regulation on health and safety at work, SOR/86-304, Part XII (12.9), and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke.

Respiratory protection Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls Not regarded as dangerous for the environment.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Liquid.
Color	Light yellow.
Odor	Mild hydrocarbon.
Odor threshold	Not available.

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	252-264°C Cleveland open cup. [ASTM D 92]
Evaporation rate	Not available.
Upper/lower flammability or explosive limits	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	0.8393-0.8468
Solubility(ies)	Not known.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	33.6-68.7 cSt @ 40°C 6.2-10.5 cSt @ 100°C [ASTM D 445]
Explosive properties	Not considered to be explosive.
Oxidizing properties	Does not meet the criteria for classification as oxidizing.
Fire point	274-276°C Cleveland open cup. [ASTM D 92]
Pour point	-40-(-53)°C [ASTM D 97]

10. Stability and reactivity

Reactivity	See the other subsections of this section for further details.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	No potentially hazardous reactions known.
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Toxicological effects	Not regarded as a health hazard under current legislation.
Acute toxicity - oral	
Notes (oral LD₅₀)	Based on available data the classification criteria are not met.

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitization

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Skin sensitization Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion

Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation.

Skin Contact

Prolonged contact may cause dryness of the skin.

Eye contact

May cause temporary eye irritation.

Route of exposure

Ingestion Inhalation Skin and/or eye contact

Target Organs

No specific target organs known.

Medical considerations

Skin disorders and allergies.

12. Ecological information

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil I

Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
Toxicity	Based on available data the classification criteria are not met.
<u>Persistence and degradability</u>	
Persistence and degradability	The degradability of the product is not known.
<u>Bioaccumulative potential</u>	
Bio-Accumulative Potential	No data available on bioaccumulation.
Partition coefficient	Not available.
<u>Mobility in soil</u>	
Mobility	No data available.
<u>Other adverse effects</u>	
Other adverse effects	None known.

13. Disposal considerations

Waste treatment methods

General information	The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements.
Disposal methods	Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste packaging should be collected for reuse or recycling. Incineration or landfill should only be considered when recycling is not feasible. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of the local water authority.

14. Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, DOT, TDG).
<u>UN Number</u>	
UN No. (International)	Not applicable.
<u>UN proper shipping name</u>	
Proper shipping name (International)	Not applicable.
<u>Transport hazard class(es)</u>	
Transport labels	
No transport warning sign required.	
<u>Packing group</u>	
Packing group (International)	Not applicable.
<u>Environmental hazards</u>	

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

Environmentally Hazardous Substance

No.

Special precautions for user

Not applicable.

DOT TIH Zone Not applicable.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

Regulatory References OSHA Hazard Communication Standard 29 CFR §1910.1200 Hazardous Products Regulation (SOR/2015-17) Transportation of Dangerous Goods Regulations -SOR/2015-100.

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

The following ingredients are listed or exempt:

Ethylbenzene

Final CERCLA RQ: 1000(454) pounds (Kilograms)

Naphthalene

Final CERCLA RQ: 100(45.4) pounds (Kilograms)

Benzene

Final CERCLA RQ: 10(4.54) pounds (Kilograms)

Xylene

Final CERCLA RQ: 100(45.4) pounds (Kilograms)

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

The following ingredients are listed or exempt:

Ethylbenzene

0.1 %

Naphthalene

0.1 %

Benzene

0.1 %

Xylene

1.0 %

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

The following ingredients are listed or exempt:

Ethylbenzene
Carcinogen.

Benzene.
Carcinogen, developmental toxin and reproductive toxin.

Naphthalene
Carcinogen.

California Air Toxics "Hot Spots" (A-I)

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

2,6-Di-tert-butyl-p-cresol

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

2,6-Di-tert-butyl-p-cresol

Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

2,6-Di-tert-butyl-p-cresol

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

2,6-Di-tert-butyl-p-cresol

New Jersey "Right To Know" List

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

2,6-Di-tert-butyl-p-cresol

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

Ethylbenzene

Naphthalene

Benzene

Xylene

2,6-Di-tert-butyl-p-cresol

Inventories

Canada - DSL/NDSL

All the ingredients are listed or exempt.

US - TSCA

All the ingredients are listed or exempt.

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

16. Other information

Synthetic GBC ISO-32, ISO-46, ISO-68 Synthetic Gear, Bearing, Compressor Oil

Abbreviations and acronyms used in the safety data sheet	C.A.S. = Chemical Abstracts Service; E.C. No = European Commission number; GHS = Globally Harmonised System; OSHA = Occupational Safety and Health Administration; WHMIS = Workplace Hazardous Materials Information System; DOT = Department of Transport; TDG = Transport of Dangerous Goods Regulations; IMDG = International Maritime Dangerous Goods; IATA = International Air Transport Association; SARA = Superfund Amendments and Reauthorization Act; CERCLA = Comprehensive Environmental; EPCRA = Emergency Planning and Community Right-to-Know Act; TSCA = Toxic Substances Control Act; LD/LC/EC = Lethal Dose, Lethal Concentration/Effect Concentration for 50% of population; NOEC = No Overall Effect Concentration; NOEL = No Overall Effect Level; REACH = Registration, Evaluation, Authorisation & Restriction of Chemicals; STOT-RE = Single Target Organ Toxicity - Repeat Exposure; STOT-SE = Specific Target Organ Toxicity - Single Exposure; PBT = Persistent, Bioaccumulative, Toxic; vPvB = Very Persistent, Very Bioaccumulative.
Key literature references and sources for data	Source: European Chemicals Agency, http://echa.europa.eu/
Training advice	Read and follow manufacturer's recommendations. Only trained personnel should use this material.
Revision comments	This is the first issue.
Revision date	6/11/2019
SDS No.	8692

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.