

Revision Date 9-July-2018  
Version 3

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

GHS product identifier : Synthetic 5w30 HP Euro Engine Oil  
Code : 018  
Product type : Liquid.

### Identified uses

Lubricating oil. Not to be misted.

### Details of the supplier of the safety data sheet

Manufacturer Address : U.S. Lubricants A Division of U.S. Venture, Inc.  
425 Better Way  
Appleton, WI 54915

### Emergency telephone number

Company Phone Number 800-490-4900  
24 Hour Emergency Phone Number 800-424-9300 (CHEMTREC 705487)

## 2. HAZARDS IDENTIFICATION

OSHA/HCS status : This material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Classification of the substance or mixture : Not classified.

### GHS label elements

Signal word : No signal word.  
Hazard statements : No known significant effects or critical hazards.

### Precautionary statements

Prevention : Not applicable.  
Response : Not applicable.  
Storage : Not applicable.  
Disposal : Not applicable.  
Hazards : None known.

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance/mixture : Mixture  
Other means of identification : Not available.

### CAS number/other identifiers

CAS number : Not applicable.  
Product code : 018

Ingredient name	%	CAS number
Base Oil(s)	10 – 30	-

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

#### 4. FIRST AID MEASURES

##### Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.
- Skin contact** : Flush contaminated skin with plenty of water. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

##### Most important symptoms/effects, acute and delayed

###### Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

###### Over-exposure signs/symptoms

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

##### Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No special protection is required.

See toxicological information (Section 11)

#### 5. FIRE-FIGHTING MEASURES

##### Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.
- Specific hazards arising from the chemical** : No specific fire or explosion hazard.
- Hazardous thermal decomposition products** : No specific data.
- Special protective actions for fire-fighters** : No special protection is required.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

## 6. ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel** : Put on appropriate personal protective equipment.

**For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For nonemergency personnel".

**Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### Methods and materials for containment and cleaning up

**Spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Protective measures** : Put on appropriate personal protective equipment (see Section 8). Avoid contact with used product. Do not reuse container.

**Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.

**Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

#### Occupational exposure limits

Under conditions which may generate mists, the following exposure limits are recommended:

ACGIH TLV TWA: 5 mg/m<sup>3</sup>; STEL: 10 mg/m<sup>3</sup>.

#### United States

None known.

#### Canada

None known.

**Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.

**Individual protection measures**

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Not required under normal conditions of use.

**9. PHYSICAL AND CHEMICAL PROPERTIES****Appearance**

- Physical state** : Liquid.
- Color** : Amber.
- Odor** : Mild hydrocarbon.
- Odor threshold** : Not available.
- pH** : Not available.
- Melting point / Pour point** : -50°C (-58°F)
- Boiling point** : Not available.
- Flash point** : Open cup: 226°C (438.8°F) [Cleveland.]
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Not available.
- Lower and upper explosive (flammable) limits** : Not available.
- Vapor pressure** : Not available.
- Vapor density** : Not available.
- Relative density** : 0.8514
- Solubility** : Not available.
- Partition coefficient: n-octanol/ water** : Not available.
- Auto-ignition temperature** : Not available.
- Decomposition temperature** : Not available.
- Viscosity** : Kinematic: 0.117 cm<sup>2</sup>/s (11.7 cSt) (100°C)  
Kinematic: 0.691 cm<sup>2</sup>/s (69.1 cSt) (40°C)
- Volatility** : Not available.
- VOC (w/w)** : 72% (w/w)

**10. STABILITY AND REACTIVITY**

- Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- Chemical stability** : The product is stable.
- Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.

- Conditions to avoid** : No specific data.
- Incompatible materials** : Reactive or incompatible with the following materials: oxidizing materials.
- Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

**11. TOXICOLOGICAL INFORMATION**

**Information on toxicological effects**

**Acute toxicity**

There is no data available.

**Irritation/Corrosion**

There is no data available.

**Sensitization**

There is no data available.

**Carcinogenicity**

There is no data available.

**Specific target organ toxicity (single exposure)**

There is no data available.

**Specific target organ toxicity (repeated exposure)**

There is no data available

**Aspiration hazard**

Name	Result
Base oil(s)	ASPIRATION HAZARD - Category 1

- Information on the likely routes of exposure** : Dermal contact. Eye contact. Inhalation. Ingestion.

**Potential acute health effects**

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

**Symptoms related to the physical, chemical and toxicological characteristics**

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

**Delayed and immediate effects and also chronic effects from short and long term exposure**

**Short term exposure**

- Potential immediate effects** : No known significant effects or critical hazards.
- Potential delayed effects** : No known significant effects or critical hazards.

**Long term exposure**

- Potential immediate effects** : No known significant effects or critical hazards.
- Potential delayed effects** : No known significant effects or critical hazards.

**Potential chronic health effects**

- General** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Teratogenicity** : No known significant effects or critical hazards.
- Developmental effects** : No known significant effects or critical hazards.
- Fertility effects** : No known significant effects or critical hazards.

**Numerical measures of toxicity****Acute toxicity estimates**

There is no data available.

**12. ECOLOGICAL INFORMATION****Toxicity**

There is no data available.

**Persistence and degradability**

There is no data available.

**Bioaccumulative potential**

There is no data available

**Mobility in soil****Soil/water partition coefficient** : There is no data available.**(K<sub>oc</sub>)****Other adverse effects** : No known significant effects or critical hazards.**13. DISPOSAL CONSIDERATIONS**

**Disposal methods** : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

**14. TRANSPORT INFORMATION**

	<b>DOT Classification</b>	<b>TGD</b>	<b>IMDG</b>	<b>IATA</b>
<b>UN number</b>	Not regulated.	Not regulated	Not regulated.	Not regulated.
<b>UN proper shipping name</b>	-	-	-	-
<b>Transport hazard class(es)</b>	-	-	-	-
<b>Packing group</b>	-	-	-	-
<b>Environmental hazards</b>	No.	No.	No.	No.
<b>Additional information</b>	-	-	-	-

**AERG:** Not applicable.

**Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

**Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code** : Not available.

**15. REGULATORY INFORMATION**

**U.S. Federal regulations** : **United States inventory (TSCA 8b):** All components are listed or exempted.  
**Clean Water Act (CWA) 307:** Phosphorodithioic acid, mixed O, O-bis(1,3-dimethylbutyl and iso-Pr) esters, zinc salts; Benzene

**Clean Water Act (CWA) 311:** Benzene; Vinyl acetate

**Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)** : Not listed

**Clean Air Act Section 602 Class I Substances** : Not listed

**Clean Air Act Section 602 Class II Substances** : Not listed

**DEA List I Chemicals (Precursor Chemicals)** : Not listed

**DEA List II Chemicals (Essential Chemicals)** : Not listed

**SARA 302/304**  
**Composition/information on ingredients**

Name	%	EHS	SARA 302 TPQ		SARA 304 RQ	
			(lbs)	(gallons)	(lbs)	(gallons)
Vinyl acetate	0 – 0.1	Yes.	1000	129	5000	644.8

**SARA 304 RQ** : 34293552.8 lbs / 15569273 kg [4830827.8 gal / 18286672.5 L]

**SARA 311/312 Classification** : Not applicable.

**SARA 313**  
No products were found.

**State Regulations**  
**Massachusetts** : None of the components are listed.  
**New York** : None of the components are listed.  
**New Jersey** : The following components are listed: Base oil(s)  
**Pennsylvania** : None of the components are listed.

**California Prop. 65**  
**WARNING:** This product contains less than 0.1% of a chemical known to the State of California to cause cancer.  
**WARNING:** This product contains less than 1% of a chemical known to the State of California to cause birth defects or other reproductive harm.

Ingredient name	Cancer	Reproductive	No significant risk level	Maximum acceptable dosage level
Benzene	Yes.	Yes.	6.4 µg/day (ingestion) 13 µg/day (inhalation)	24 µg/day (ingestion) 49 µg/day (inhalation)
Trace Metals	Yes.	Yes.	No.	No.
Vinyl acetate	Yes.	No.	No.	No.

**Canada**  
**Canadian lists**  
**Canadian NPRI** : None of the components are listed.  
**CEPA Toxic substances** : None of the components are listed.  
**Canada inventory** : All components are listed or exempted.

**16. OTHER INFORMATION****History**

**Date of issue mm/dd/yyyy** : 07/09/2018  
**Date of previous issue** : 09/15/2015  
**Version** : 3  
**Prepared by** : US Lubricants

**Notice to reader**

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

**End of Safety Data Sheet**