

SAFETY DATA SHEET

1. Identification

Blue Wolf

Sodium Hypochlorite Solution, 10-16%

Product identifier

Other means of identification

SDS number

502-USA-OLN

Synonyms

Tri-Lite® 100, Tri-lite® 150, Tri-lite® 160, Tri-Lite® 200, Sodium Hypochlorite 12.5%, Bleach, Hypochlorite solution, Liquid bleach, Soda bleach solution, Sodium Hypochlorite 10%

Recommended use

Biocide. Bleaching agent. Disinfectant. Water treatment.

Recommended restrictions

None known.

Manufacturer/Importer/Supplier/Distributor information

Company name

Blue Wolf Sales and Service, Inc.

Address

219 Industrial Park Road
Bluefield, Virginia 24605

Telephone

855-803-1417

E-mail

sales@bluewolfcleaner.com

Emergency phone number

CHEMTREC (US/Canada) 1-800-424-9300
CHEMTREC (International) +1 703-527-3887 (collect calls accepted)

2. Hazard(s) identification

Physical hazards

Corrosive to metals Category 1

Health hazards

Skin corrosion/irritation Category 1

Serious eye damage/eye irritation Category 1

Specific target organ toxicity, single exposure Category 3 (respiratory tract irritation)

Environmental hazards

Hazardous to the aquatic environment, acute hazard Category 1

Hazardous to the aquatic environment, long-term hazard Category 2

OSHA defined hazards

Not classified.

Label elements



Signal word

DANGER

Hazard statement

May be corrosive to metals. Causes severe skin burns and eye damage. May cause respiratory irritation. Toxic to aquatic life with long lasting effects.

Precautionary statement

Prevention

Wear protective gloves/protective clothing/eye protection/face protection. Do not breathe mist or vapor. Use only outdoors or in a well-ventilated area. Wash hands thoroughly after handling. Keep only in original container. Avoid release to the environment.

Response

IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

IN INHALED: Remove person to fresh air and keep comfortable for breathing.

IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center/doctor.

Wash contaminated clothing before reuse. Absorb/collect spillage to prevent material damage.

Storage

Store in a well-ventilated place. Keep container tightly closed. Store locked up. Store in corrosive resistant container with a resistant inner liner.

Disposal

Dispose of contents/container in accordance with local/regional/national/international regulations.

Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	Contact with acids liberates toxic gas.

3. Composition/information on ingredients

Mixtures

Chemical name	CAS number	%
Sodium hypochlorite	7681-52-9	10 - 16
Sodium hydroxide	1310-73-2	0.2 - 1.0
Water	7732-18-5	Balance

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Take off immediately all contaminated clothing. Wash off IMMEDIATELY with plenty of water for at least 15-20 minutes. Get medical attention immediately. Wash contaminated clothing before reuse. Call a physician or poison control center immediately.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention immediately.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Corrosive effects. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result.
Indication of immediate medical attention and special treatment needed	Treat symptomatically. Chemical burns: Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. With eye exposure, continue flushing during transport to hospital.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire. Do not use dry extinguishing media that contains ammonium compounds.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Wear appropriate personal protective equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Absorb spillage to prevent material damage. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Do not discharge into drains, water courses or onto the ground. Environmental manager must be informed of all major releases. See Section 14 for RQ reporting information.

7. Handling and storage

Precautions for safe handling

Wear appropriate personal protective equipment. Do not get in eyes, on skin, on clothing. Use with adequate ventilation. Observe good industrial hygiene practices. Do not apply heat or direct sunlight. Temperature and product concentration affect product quality and decomposition rates.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed. Store in a cool, dry, well-ventilated place. Store in a corrosive resistant container. Consult container manufacturer for additional guidance. Store away from and do not mix with incompatible materials such as acids, oxidizers, organics, reducing agents, and all metals except titanium.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Sodium hydroxide (CAS 1310-73-2)	PEL	2 mg/m ³

US. ACGIH Threshold Limit Values

Components	Type	Value
Sodium hydroxide (CAS 1310-73-2)	Ceiling	2 mg/m ³

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Sodium hydroxide (CAS 1310-73-2)	Ceiling	2 mg/m ³

US. Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value
Sodium hypochlorite (CAS 7681-52-9)	STEL	2 mg/m ³

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear safety glasses with side shields (or goggles) and a face shield. Wear a full-face respirator, if needed.

Skin protection

Hand protection

Wear appropriate chemical resistant gloves.

Other

Wear appropriate chemical resistant clothing. Reports indicate that sodium hypochlorite can react with various fabrics usually increasing with concentration. Reactions vary significantly depending on strength of chemical, material, fabric treatment and color of dyes. FRC treated cotton has a stronger response than plain cotton. Poly blend fabrics and meta aramid fabric have a weaker response than natural fibers. Contact the Personal Protective Equipment manufacturer for specific information about their products.

Respiratory protection

If engineering controls do not maintain airborne concentrations below recommended exposure limits (where applicable) or to an acceptable level (in countries where exposure limits have not been established), an approved respirator must be worn.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance Clear.

Physical state Liquid.

Form Liquid.

Color Pale yellow - Straw colored

Odor	Chlorine-like.
Odor threshold	0.9 mg/m ³
pH	13
Melting point/freezing point	-17 °F (-27.22 °C)
Initial boiling point and boiling range	231.8 °F (111 °C)
Flash point	Not relevant.
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not relevant.
Flammability limit - upper (%)	Not relevant.
Explosive limit - lower (%)	Not relevant.
Explosive limit - upper (%)	Not relevant.
Vapor pressure	12 mmHg @ 20 °C (68 °F) for 12.5 % by weight solution
Vapor density	Not available.
Relative density	1.163 @ 15.5 °C (60 °F) (Weight % Available Chlorine = 10.34) 1.203 @ 15.5 °C (60 °F) (Weight % Available Chlorine = 12.52) 1.216 @ 15.5 °C (60 °F) (Weight % Available Chlorine = 13.19) 1.255 @ 15.5 °C (60 °F) (Weight % Available Chlorine = 15.14)
Solubility(ies)	
Solubility (water)	100 %
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Bulk density	1.16 - 1.25 g/cm ³ 9.7 lb/gal @ 15.5 °C (60 °F) (Weight % Available Chlorine = 10.34) 10.03 lb/gal @ 15.5 °C (60 °F) (Weight % Available Chlorine = 12.52) 10.14 lb/gal @ 15.5 °C (60 °F) (Weight % Available Chlorine = 13.19) 10.46 lb/gal @ 15.5 °C (60 °F) (Weight % Available Chlorine = 15.14)
Molecular formula	NaOCl
Molecular weight	74.5 g/mol

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Contact with incompatible materials. Avoid ultraviolet (UV) light sources. Excessive heat. Reacts violently with strong acids. Acid contact will produce chlorine gas. Amine contact will produce chloramines.
Incompatible materials	Strong oxidizing agents. Acids. Metals. Organic compounds. Ammonia.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Vapors and spray mist may irritate throat and respiratory system and cause coughing.
-------------------	--

Skin contact Causes skin burns.
Eye contact Causes eye burns.
Ingestion Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Ingestion may produce burns to the lips, oral cavity, upper airway, esophagus and possibly the digestive tract.
Symptoms related to the physical, chemical and toxicological characteristics Corrosive effects. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result.

Information on toxicological effects

Acute toxicity Occupational exposure to the substance or mixture may cause adverse effects.

Product	Species	Test Results
Sodium Hypochlorite Solution, 10-16% (CAS Mixture)		
Acute		
Dermal, LD50	Rabbit	3000 - 10000 mg/kg
Oral, LD50	Rat	8200 mg/kg

Skin corrosion/irritation Causes severe skin burns and eye damage.

Serious eye damage/eye irritation Causes serious eye damage.

Respiratory or skin sensitization

Respiratory sensitization Not classified.

Skin sensitization Not classified.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

Sodium hypochlorite (CAS 7681-52-9) 3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Reproductive toxicity Not classified.

Specific target organ toxicity - single exposure May cause respiratory irritation.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not classified, however droplets of the product may be aspirated into the lungs through ingestion or vomiting and may cause a serious chemical pneumonia.

Chronic effects Prolonged or repeated overexposure causes lung damage.

Further information Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity Toxic to aquatic life with long lasting effects. Low in toxicity to avian wildlife.

Product	Species	Test Results	
Sodium Hypochlorite Solution, 10-16%			
Aquatic			
Crustacea	EC50	Daphnia magna	0.033 - 0.044 mg/l, 48 Hours
	LC50	Daphnia magna	2.1 mg/l, 96 Hours
Fish	LC50	Bluegill (Lepomis macrochirus)	0.6 mg/l, 48 Hours

Persistence and degradability The product contains inorganic compounds which are not biodegradable. Degrades slowly to sodium chloride, sodium chlorate and oxygen.

Bioaccumulative potential The product is not expected to bioaccumulate.

Mobility in soil No data available.

Other adverse effects None known.

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. This material and its container must be disposed of as hazardous waste. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT	
UN number	UN1791
UN proper shipping name	Hypochlorite solutions
Transport hazard class(es)	
Class	8
Subsidiary risk	-
Label(s)	8
Packing group	III
Environmental hazards	
Marine pollutant	Yes (Sodium hypochlorite solution)
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	IB3, N34, T4, TP2, TP24
Packaging exceptions	154
Packaging non bulk / bulk	203 / 241
RQ	100 lbs. (Sodium Hypochlorite) For gallons of product equivalent to 100 lbs of available sodium hypochlorite, use the following: 98.7 gallons 10% by weight product, 75.9 gallons for 12.5% by weight, 72.5 gallons for 13% by weight, 60.8 gallons for 15% by weight.
IATA	
UN number	UN1791
UN proper shipping name	Hypochlorite solution
Transport hazard class(es)	
Class	8
Subsidiary risk	
Packing group	- III
Environmental hazards	Yes
ERG Code	8L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
IMDG	
UN number	UN1791
UN proper shipping name	HYPOCHLORITE SOLUTION
Transport hazard class(es)	
Class	8
Subsidiary risk	-
Packing group	III
Environmental hazards	
Marine pollutant	Yes
EmS	F-A, S-B
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling

Transport in bulk according To Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

US federal regulations

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

Sodium hydroxide (CAS 1310-73-2) LISTED

Sodium hypochlorite (CAS 7681-52-9) LISTED

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes

Delayed Hazard - No

Fire Hazard - No

Pressure Hazard - No

Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical

Yes

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)

Not regulated.

US state regulations

US. Massachusetts RTK - Substance List

Sodium hydroxide (CAS 1310-73-2)

Sodium hypochlorite (CAS 7681-52-9)

US. New Jersey Worker and Community Right-to-Know Act

Sodium hydroxide (CAS 1310-73-2)

Sodium hypochlorite (CAS 7681-52-9)

US. Pennsylvania Worker and Community Right-to-Know Law

Sodium hydroxide (CAS 1310-73-2)

Sodium hypochlorite (CAS 7681-52-9)

US. Rhode Island RTK

Sodium hydroxide (CAS 1310-73-2)

Sodium hypochlorite (CAS 7681-52-9)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

International Inventories

Sodium Hypochlorite Solution, 10-16%

Version #: 04

Revision date: 21-August-2015

SDS US

7 / 8

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	No Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

* A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	1-January-2015		
Revision date	21-August-2015		
Version #	04		
Revision History			
02-17-15	Section 14	Added information for RQ calculation	
03-10-15	Section 14	Added "solution" to name of Marine Pollutant for US DOT transport information	
08-21-15	Section 2	Added missing hazard statement "Causes severe skin burns and eye damage"	

Further information NFPA Hazard Scale: 0 = Minimal 1 = Slight 2 = Moderate 3 = Serious 4 = Severe

NFPA ratings



List of abbreviations
LD50: Lethal Dose, 50%.
LC50: Lethal Concentration, 50%.
EC50: Effective concentration, 50%.
TWA: Time weighted average.

References
EPA: AQUIRE database
HSDB® - Hazardous Substances Data Bank
US. IARC Monographs on Occupational Exposures to Chemical Agents
IARC Monographs. Overall Evaluation of Carcinogenicity
ACGIH Documentation of the Threshold Limit Values and Biological Exposure Indices (2009)

Disclaimer
Blue Wolf Sales & Service Inc. cannot anticipate all the conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.