

SAFETY DATA SHEET

SECTION 1) CHEMICAL PRODUCT AND SUPPLIER'S IDENTIFICATION

Product ID : PBW-BP
Product Name : Blue Wolf Blaster
Revision Date : Nov 21, 2016 **Supersedes Date :** Jun 30, 2015
Version: 1.0
Distributor's Name: BLUE WOLF SALES & SERVICE, INC
Address : 219 INDUSTRIAL PARK ROAD - BLUEFIELD, VA 24605
Emergency Phone : 1-800-535-5053
Information Phone : (855) 803-1417
Fax :
Product/Recommended Uses: Non-Flammable Lubricant/Penetrant

SECTION 2) HAZARDS IDENTIFICATION

Classification:

Skin Irritation - Category 2
Carcinogenicity - Category 2
Chronic aquatic toxicity - Category 2
Acute aquatic toxicity - Category 2
Aerosol - Category 3

Pictograms:



Signal Word:

Warning

Hazardous Statements - Physical:

H229 - Pressurised container: May burst if heated

Hazardous Statements - Health:

H351 - Suspected of causing cancer.

H315 - Causes skin irritation

Hazardous Statements - Environmental:

H411 - Toxic to aquatic life with long lasting effects

Precautionary Statements - General:

P101 - If medical advice is needed, have product container or label at hand.

P102 - Keep out of reach of children.

P103 - Read label before use.

Precautionary Statements - Prevention:

P273 - Avoid release to the environment.

P280 - Wear protective gloves/protective clothing/eye protection/face protection.

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P264 - Wash thoroughly after handling.

P251 - Do not pierce or burn, even after use.

Precautionary Statements - Response:

P308 + P313 - IF exposed or concerned: Get medical advice/attention.

P391 - Collect spillage.

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water.

P332 + P313 - If skin irritation occurs: Get medical advice/attention.

P362 + P364 - Take off contaminated clothing and wash it before reuse.

Precautionary Statements - Storage:

P405 - Store locked up.

P410 - Protect from sunlight.

P412 - Do not expose to temperatures exceeding 50 °C/122 °F.

Precautionary Statements - Disposal:

P501 - Dispose of contents and container in accordance with all local, regional, national and international regulations.

SECTION 3) COMPOSITION / INFORMATION ON INGREDIENTS

CAS	Chemical Name	% by Weight
0000127-18-4	TETRACHLOROETHYLENE	55% - 88%
0064742-65-0	MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT-DEWAXED HEAVY PARAFFINIC	6% - 14%
0000111-76-2	ETHYLENE GLYCOL MONOBUTYL ETHER	1% - 3%
0000124-38-9	CO2	1% - 3%

SECTION 4) FIRST-AID MEASURES

Inhalation:

Remove source of exposure or move person to fresh air and keep comfortable for breathing.

If exposed/feel unwell/concerned: Call a POISON CENTER/doctor.

Eliminate all ignition sources if safe to do so.

Eye Contact:

Remove source of exposure or move person to fresh air. Rinse eyes cautiously with lukewarm, gently flowing water for several minutes, while holding the eyelids open. Remove contact lenses, if present and easy to do. Continue rinsing for a duration of 15-20 minutes. Take care not to rinse contaminated water into the unaffected eye or onto the face. If eye irritation persists: Get medical advice/attention.

Skin Contact:

Take off immediately all contaminated clothing, shoes and leather goods (e.g. watchbands, belts). Gently blot or brush away excess product. Wash with plenty of lukewarm, gently flowing water for a duration of 15-20 minutes. Call a POISON CENTER/doctor if you feel unwell. Store contaminated clothing under water and wash before reuse or discard.

Ingestion:

Rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTER/doctor. If vomiting occurs naturally, lie on your side, in the recovery position.

Never give anything by mouth to an unconscious or convulsing victim. Keep person warm and quiet.

SECTION 5) FIRE-FIGHTING MEASURES

Suitable Extinguishing Media:

Will not burn. Use extinguishing media suitable for surrounding fire.

Unsuitable Extinguishing Media:

Water may be ineffective but can be used to cool containers exposed to heat or flame.

Specific Hazards in Case of Fire:

Contents under pressure. Keep away from ignition sources and open flames. Exposure of containers to extreme heat and flames can cause them to rupture often with violent force.

Aerosol cans may rupture when heated.
Heated cans may burst.

In fire, will decompose to carbon dioxide, carbon monoxide

Fire-Fighting Procedures:

Isolate immediate hazard area and keep unauthorized personnel out. Stop spill/release if it can be done safely. Move undamaged containers from immediate hazard area if it can be done safely. Water spray may be useful in minimizing or dispersing vapors and to protect personnel.

Dispose of fire debris and contaminated extinguishing water in accordance with official regulations.

Special Protective Actions:

Wear protective pressure self-contained breathing apparatus (SCBA) and full turnout gear.

Care should always be exercised in dust/mist areas.

SECTION 6) ACCIDENTAL RELEASE MEASURES

Emergency Procedure:

ELIMINATE all ignition sources (no smoking, flares, sparks, or flames in immediate area). Stay upwind; keep out of low areas. Immediately turn off or isolate any source of ignition. Keep unnecessary people away; isolate hazard area and deny entry. Do not touch or walk through spilled material. Clean up immediately. Use absorbent sweeping compound to soak up material and put into suitable container for proper disposal.

Recommended Equipment:

Wear safety glasses and gloves.

Personal Precautions:

ELIMINATE all ignition sources (no smoking, flares, sparks, or flames in immediate area). Use explosion proof equipment. Avoid breathing vapor. Avoid contact with skin, eye or clothing. Do not touch damaged containers or spilled materials unless wearing appropriate protective clothing.

Environmental Precautions:

Stop spill/release if it can be done safely. Prevent spilled material from entering sewers, storm drains, other unauthorized drainage systems and natural waterways by using sand, earth, or other appropriate barriers.

SECTION 7) HANDLING AND STORAGE

General:

For industrial and institutional use only.
For use by trained personnel only.
Keep away from children.
Wash hands after use.
Do not get in eyes, on skin or on clothing.
Do not breathe vapors or mists.
Use good personal hygiene practices.
Eating, drinking and smoking in work areas is prohibited.
Remove contaminated clothing and protective equipment before entering eating areas.
Eyewash stations and showers should be available in areas where this material is used and stored.

Ventilation Requirements:

Use only with adequate ventilation to control air contaminants to their exposure limits. The use of local ventilation is recommended to control emissions near the source.

Storage Room Requirements:

Keep container(s) tightly closed and properly labeled. Store in cool, dry, well-ventilated areas away from heat, direct sunlight and incompatibilities. Store in approved containers and protect against physical damage. Keep containers securely sealed when not in use. Indoor storage should meet OSHA standards and appropriate fire codes. Containers that have been opened must be carefully resealed to prevent leakage. Empty container retain residue and may be dangerous.

Do not cut, drill, grind, weld, or perform similar operations on or near containers. Do not pressurize containers to empty them. Ground all structures, transfer containers and equipment to conform to the national electrical code. Use procedures that prevent static electrical sparks. Static electricity may accumulate and create a fire hazard.

Store at temperatures below 120°F.

SECTION 8) EXPOSURE CONTROLS, PERSONAL PROTECTION

Eye Protection:

Chemical goggles, safety glasses with side shields or vented/splash proof goggles. Contact lenses may absorb irritants. Particles may adhere to lenses and cause corneal damage.

Skin Protection:

Wear gloves, long sleeved shirt, long pants and other protective clothing as required to minimize skin contact.

Use of gloves approved to relevant standards made from the following materials may provide suitable chemical protection: PVC, neoprene or nitrile rubber gloves. Suitability and durability of a glove is dependent on usage, e.g. frequency and duration of contact, chemical resistance of glove material, glove thickness, dexterity. Always seek advice from glove suppliers. Contaminated gloves should be replaced. Chemical-resistant clothing is recommended to avoid prolonged contact. Avoid unnecessary skin contact.

Respiratory Protection:

If engineering controls do not maintain airborne concentrations to a level which is adequate to protect worker, a respiratory protection program that meets or is equivalent to OSHA 29 CFR 1910.134 and ANSI Z88.2 should be followed. Check with respiratory protective equipment suppliers. Where air-filtering respirators are suitable, select an appropriate combination of mask and filter. Select a filter suitable for combined particulate/organic gases and vapors.

When spraying more than one half can continuously or more than one can consecutively, use NIOSH approved respirator.

Chemical Name	OSHA TWA (ppm)	OSHA TWA (mg/m3)	OSHA STEL (ppm)	OSHA STEL (mg/m3)	OSHA-Tables-Z1,2,3	OSHA Carcinogen	OSHA Skin designation	NIOSH TWA (ppm)	NIOSH TWA (mg/m3)	NIOSH STEL (ppm)	NIOSH STEL (mg/m3)	NIOSH Carcinogen
CO2	5000	9000			1			5000	9000	30000	54000	
ETHYLENE GLYCOL MONOBUTYL ETHER	50	240			1		1	5	24			
MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT-DEWAXED HEAVY PARAFFINIC	500	2000			1							
TETRACHLOROETHYLENE	100 (a)/ 200 ceiling		300ppm /5 mins. in any 3 hrs. (a)		1,2			b				1

Chemical Name	ACGIH TWA (ppm)	ACGIH TWA (mg/m3)	ACGIH STEL (ppm)	ACGIH STEL (mg/m3)
CO2	5000	9000	30000	54000
ETHYLENE GLYCOL MONOBUTYL ETHER	20	97		
MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT-DEWAXED HEAVY PARAFFINIC				
TETRACHLOROETHYLENE	25	170	100	685

SECTION 9) PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Density	11.11951 lb/gal
Density VOC	0.24596 lb/gal
% VOC	2.21192%

VOC Actual 0.24596 lb/gal

VOC Actual 29.47281 g/l

Appearance	Dark liquid
Odor Threshold	N.A.
Odor Description	Strawberry
pH	N.A.
Water Solubility	Nil
Flammability	Will not burn
Flash Point Symbol	N.A.
Flash Point	N.A.
Viscosity	N.A.
Lower Explosion Level	N.A.
Upper Explosion Level	N.A.
Melting Point	N.A.
Vapor Density	Slower than ether
Freezing Point	N.A.
Low Boiling Point	0 °F
High Boiling Point	343 °F
Decomposition Pt	0
Auto Ignition Temp	N.A.
Evaporation Rate	Slower than ether

SECTION 10) STABILITY AND REACTIVITY

Stability:

Stable.

Conditions to Avoid:

High temperatures.

Incompatible Materials:

None known.

Hazardous Reactions/Polymerization:

Will not occur.

Hazardous Decomposition Products:

In fire, will decompose to carbon dioxide, carbon monoxide.

SECTION 11) TOXICOLOGICAL INFORMATION

Skin Corrosion/Irritation:

Overexposure will cause defatting of skin.

Serious Eye Damage/Irritation:

Overexposure will cause redness and burning sensation.

Carcinogenicity:

Suspected of causing cancer.

Germ Cell Mutagenicity:

No data available

Reproductive Toxicity:

No data available

Respiratory/Skin Sensitization:

No data available

Specific Target Organ Toxicity - Single Exposure:

No data available

Specific Target Organ Toxicity - Repeated Exposure:

No data available

Aspiration Hazard:

No data available

Acute Toxicity:

Inhalation: effect of overexposure include irritation of respiratory tract, headache, dizziness, nausea, and loss of coordination. Extreme overexposure may result in unconsciousness and possibly death.

0064742-65-0 MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT-DEWAXED HEAVY PARAFFINIC

LD50 (Rodent - rat, Oral) : >5000 mg/kg, Toxic effects : Details of toxic effects not reported other than lethal dose value.

LD50 (Rodent - rabbit, Administration onto the skin) : 5000 mg/kg, Toxic effects : Details of toxic effects not reported other than lethal dose value.

0000127-18-4 TETRACHLOROETHYLENE

LC50 (rat): Approximately 3786 ppm (4-hour exposure) (22); approximately 4000 ppm (4-hour exposure) (23)

LC50 (mouse): 5200 ppm (4-hour exposure) (24)

LD50 (oral, rat): Approximately 2600 mg/kg (cited as 1.6 mL/kg) (20)

LD50 (oral, male rat): 3835 mg/kg (25)

LD50 (oral, female rat): 3005 mg/kg (25)

LD50 (dermal, rabbit): Greater than 3245 mg/kg (0/5 animals died) (2)

0000111-76-2 ETHYLENE GLYCOL MONOBUTYL ETHER

LC50 (female rat): 450 ppm (4-hour exposure) (2)

LC50 (male rat): 486 ppm (4-hour exposure) (2)

LD50 (oral, male weanling rat): 3000 mg/kg (1)

LD50 (oral, 6-week old male rat): 2400 mg/kg (1)

LD50 (oral, yearling male rat): 560 mg/kg (1)

LD50 (oral, female rat): 530 mg/kg; 2500 mg/kg (1) LD50 (oral, male mouse): 1230 mg/kg (1)

LD50 (oral, rabbit): 320 mg/kg (1)

LD50 (dermal, male rabbit): 406 mg/kg (cited as 0.45 mL/kg) (1)

Potential Health Effects - Miscellaneous

0000111-76-2 ETHYLENE GLYCOL MONOBUTYL ETHER

Can be absorbed through the skin in harmful amounts. May cause injury to the kidneys, liver, blood and/or bone marrow. Repeated overexposure may result in damage to the blood. Eye contact may cause corneal injury. Has been toxic to the fetus in laboratory animals at doses that are toxic to the mother.

SECTION 12) ECOLOGICAL INFORMATION

Toxicity:

Toxic to aquatic life with long lasting effects.

Persistence and Degradability:

No data available.

Bio-Accumulative Potential:

No data available.

Mobility in Soil:

No data available.

Other Adverse Effects:

No data available.

Bio-accumulative Potential

0064742-65-0 MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT-DEWAXED HEAVY PARAFFINIC

Contains constituents with the potential to bioaccumulate.

Mobility in Soil

0064742-65-0 MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT-DEWAXED HEAVY PARAFFINIC

Liquid under most environmental conditions. Floats on water. If it enters soil, it will adsorb to soil particles and will not be mobile.

SECTION 13) DISPOSAL CONSIDERATIONS

Water Disposal:

Under RCRA, it is the responsibility of the user of the product, to determine at the time of disposal whether the product meets RCRA criteria for hazardous waste. Waste management should be in full compliance with federal, state, and local laws.

Empty containers retain product residue which may exhibit hazards of material, therefore do not pressurize, cut, glaze, weld or use for any other purposes. Return drums to reclamation centers for proper cleaning and reuse.

SECTION 14) TRANSPORT INFORMATION

U.S. DOT Information:

Consumer Commodity, ORM-D

IMDG Information:

Consumer Commodity, ORM-D

IATA Information:

Consumer Commodity, ORM-D

SECTION 15) REGULATORY INFORMATION

CAS	Chemical Name	% By Weight	Regulation List
0000127-18-4	TETRACHLOROETHYLEN E	55% - 88%	CERCLA,HAPS,SARA312,SARA313,VOC_exempt,TSCA,RCRA,ACGIH,CA_Prop65 - California Proposition 65,OSHA
0064742-65-0	MINERAL OIL, PETROLEUM DISTILLATES, SOLVENT- DEWAXED HEAVY PARAFFINIC	6% - 14%	SARA312,TSCA,OSHA
0000111-76-2	ETHYLENE GLYCOL MONOBUTYL ETHER	1% - 3%	CERCLA,SARA312,SARA313,VOC,TSCA,ACGIH,OSHA
0000124-38-9	CO2	1% - 3%	SARA312,TSCA,ACGIH,OSHA


SECTION 16) OTHER INFORMATION

Glossary:


* There are points of differences between OSHA GHS and UN GHS. In 90% of the categories, they can be used interchangeably, but for the Skin Corrosion/Irritant Category and the Specific Target Organ Toxicity (Single and Repeated Exposure) Categories. In these cases, our system will say UN GHS.

ACGIH- American Conference of Governmental Industrial Hygienists; ANSI- American National Standards Institute; Canadian TDG- Canadian Transportation of Dangerous Goods; CAS- Chemical Abstract Service; Chemtrec- Chemical Transportation Emergency Center (US); CHIP- Chemical Hazard Information and Packaging; DSL- Domestic Substances List; EC- Equivalent Concentration; EH40 (UK)- HSE Guidance Note EH40 Occupational Exposure Limits; EPCRA- Emergency Planning and Community Right-To-Know Act; ESL- Effects screening levels; HMIS- Hazardous Material Information Service; LC- Lethal Concentration; LD- Lethal Dose; NFPA- National Fire Protection Association; OEL- Occupational Exposure Limits; OSHA- Occupational Safety and Health Administration, US Department of Labor; PEL- Permissible Exposure Limit; SARA (Title III)- Superfund Amendments and Reauthorization Act; SARA 313- Superfund Amendments and Reauthorization Act, Section 313; SCBA- Self-Contained Breathing Apparatus; STEL- Short Term Exposure Limit; TCEQ - Texas Commission on Environmental Quality; TLV- Threshold Limit Value; TSCA- Toxic Substances Control Act Public Law 94-469; TWA - Time Weighted Value; US DOT- US Department of Transportation; WHMIS- Workplace Hazardous Materials Information System.

HMIS



NFPA



Chronic :



DISCLAIMER

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist. The above information pertains to this product as currently formulated, and is based on the information available at this time. Addition of reducers or other additives to this product may substantially alter the composition and hazards of the product. Since conditions of use are outside our control, we make no warranties, express or implied, and assume no liability in connection with any use of this information.