

This safety data sheet was created pursuant to the requirements of:  
US OSHA Hazard Communication Standard (29 CFR 1910.1200) and Canada WHMIS  
2015 which includes the amended Hazardous Products Act (HPA) and the Hazardous  
Products Regulation (HPR)

Revision date 11/30/2022

Revision Number 1

## 1. Identification

### Product identifier

**Product Name** THRIVE 5W30 Dexos 1 Gen 3

### Other means of identification

**Product Code(s)** 100-055D

**Synonyms** None

**Other information** Blend Revision ID 4378

### Recommended use of the chemical and restrictions on use

**Recommended use** Lubricant

**Restrictions on use** No information available

### Details of the supplier of the safety data sheet

#### **Supplier Address**

U.S. Lubricants, a Division of U.S. Venture Inc.  
425 Better Way  
Appleton, WI 54915  
800-490-4900

### Emergency telephone number

**Emergency Telephone** 800-490-4900 Chemtrec 1-800-424-9300 (Account# 705487)

## 2. Hazard(s) identification

### Classification

Acute toxicity - Inhalation (Dusts/Mists)	Category 4
---	------------

**Appearance** No information available

**Physical state** Liquid

**Odor** Mild Petroleum

### Label elements

#### **Warning**

#### **Hazard statements**

Harmful if inhaled

**Precautionary Statements - Prevention**

Avoid breathing dust, fume, gas, mist, vapors and spray  
Use only outdoors or in a well-ventilated area

**Precautionary Statements - Response****Inhalation**

IF INHALED: Remove person to fresh air and keep comfortable for breathing  
Call a doctor if you feel unwell

**Other information**

May be harmful in contact with skin.

### 3. Composition/information on ingredients

**Substance**

Not applicable.

**Mixture**

Chemical name	CAS No	Weight-%	Hazardous Material Information Review Act registry number (HMIRA registry #)	Date HMIRA filed and date exemption granted (if applicable)
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based	72623-87-1	80-90	-	-

### 4. First-aid measures

**Description of first aid measures**

<b>General advice</b>	Show this safety data sheet to the doctor in attendance.
<b>Inhalation</b>	Remove to fresh air. If symptoms persist, call a physician. If breathing has stopped, give artificial respiration. Get medical attention immediately.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
<b>Skin contact</b>	Wash skin with soap and water.
<b>Ingestion</b>	Do NOT induce vomiting. Rinse mouth. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Self-protection of the first aider</b>	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Avoid breathing vapors or mists. Use personal protective equipment as required. See section 8 for more information.

**Most important symptoms and effects, both acute and delayed**

**Symptoms** Coughing and/ or wheezing. Difficulty in breathing.

**Indication of any immediate medical attention and special treatment needed**

**Note to physicians** Treat symptomatically.

## 5. Fire-fighting measures

**Suitable Extinguishing Media** Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Large Fire** CAUTION: Use of water spray when fighting fire may be inefficient.

**Unsuitable extinguishing media** Water spray jet.

**Specific hazards arising from the chemical** No information available.

**Hazardous combustion products** Oxides of sulfur. Aldehydes. Ketones and their derivatives. Carbon monoxide. Organic compounds.

**Explosion data**

**Sensitivity to mechanical impact** None.

**Sensitivity to static discharge** None.

**Special protective equipment and precautions for fire-fighters** Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

## 6. Accidental release measures

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Deny entry to unauthorized and unprotected personnel. Ensure adequate ventilation. Avoid breathing vapors or mists. Use personal protective equipment as required.

**Other information** Refer to protective measures listed in Sections 7 and 8.

**Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Pick up and transfer to properly labeled containers.

## 7. Handling and storage

**Precautions for safe handling**

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice. Avoid breathing vapors or mists. Ensure adequate ventilation. In case of insufficient ventilation, wear suitable respiratory equipment. Do not eat, drink or smoke when using this product.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place. Keep out of the reach of children.

**8. Exposure controls/personal protection**

**Control parameters**  
**Exposure Limits**

Chemical name	ACGIH TLV	OSHA PEL	NIOSH	
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	TWA: 5 mg/m <sup>3</sup> inhalable particulate matter excluding metal working fluids, highly & severely refined	TWA: 5 mg/m <sup>3</sup> (vacated) TWA: 5 mg/m <sup>3</sup>	IDLH: 2500 mg/m <sup>3</sup> TWA: 5 mg/m <sup>3</sup> STEL: 10 mg/m <sup>3</sup>	
Chemical name	Alberta	British Columbia	Ontario	Quebec
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	TWA: 5 mg/m <sup>3</sup> STEL: 10 mg/m <sup>3</sup>	TWA: 0.2 mg/m <sup>3</sup> TWA: 1 mg/m <sup>3</sup>	TWA: 5 mg/m <sup>3</sup> TWA:	TWA: 5 mg/m <sup>3</sup> STEL: 10 mg/m <sup>3</sup>

**Appropriate engineering controls**

**Engineering controls**                      Showers  
     Eyewash stations  
     Ventilation systems.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection**                      No special protective equipment required.

**Hand protection**                            No special protective equipment required.

**Skin and body protection**                No special protective equipment required.

**Respiratory protection**                  No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**General hygiene considerations**        Do not eat, drink or smoke when using this product.

**9. Physical and chemical properties**

**Information on basic physical and chemical properties**

**Physical state**                                Liquid  
**Appearance**                                No information available  
**Color**    amber  
**Odor**    Mild Petroleum  
**Odor threshold**                              No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
<b>pH</b>	No data available	Neutral
<b>Melting point / freezing point</b>	No data available	None known
<b>Initial boiling point and boiling range</b>	No data available	None known
<b>Flash point</b>	216 °C / 420.8 °F	
<b>Evaporation rate</b>	No data available	None known
<b>Flammability</b>	No data available	None known
<b>Flammability Limit in Air</b>		None known
<b>Upper flammability or explosive limits</b>	No data available	
<b>Lower flammability or explosive limits</b>	No data available	

Vapor pressure	No data available	None known
Relative vapor density	No data available	None known
Relative density	0.85 (7.03 lb/gal)	
Water solubility	Insoluble in water	
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	10 - 11 cSt	@ 100 °C
Dynamic viscosity	No data available	None known

**Other information**

Explosive properties	No information available
Oxidizing properties	No information available
Softening point	No information available
Molecular weight	No information available
VOC Content (%)	No information available
Liquid Density	No information available
Bulk density	No information available

**10. Stability and reactivity**

Reactivity	No information available.
Chemical stability	Stable under normal conditions.
Possibility of hazardous reactions	None under normal processing.
Conditions to avoid	Excessive heat.
Incompatible materials	None known based on information supplied.
Hazardous decomposition products	None known based on information supplied.

**11. Toxicological information****Information on likely routes of exposure****Product Information**

Inhalation	Specific test data for the substance or mixture is not available. Harmful by inhalation. (based on components).
Eye contact	Specific test data for the substance or mixture is not available.
Skin contact	May be harmful in contact with skin.
Ingestion	Specific test data for the substance or mixture is not available.

**Symptoms related to the physical, chemical and toxicological characteristics**

Symptoms	Coughing and/ or wheezing.
----------	----------------------------

**Acute toxicity****Numerical measures of toxicity**

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	5,555.60 mg/kg
ATEmix (dermal)	2,222.20 mg/kg
ATEmix (inhalation-dust/mist)	2.42 mg/l

**Component Information**

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	> 5000 mg/kg ( Rat )	> 2000 mg/kg ( Rabbit )	= 2.18 mg/L ( Rat ) 4 h

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Skin corrosion/irritation** No information available.

**Serious eye damage/eye irritation** No information available.

**Respiratory or skin sensitization** No information available.

**Germ cell mutagenicity** No information available.

**Carcinogenicity** The classification listed below for the petroleum distillates in this product pertains to those that contain more than 3% DMSO extract as measured by IP 346. The petroleum distillates in this product do not meet that criteria to be classified as carcinogens.

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	A2	-	-	-

**Legend**

**ACGIH (American Conference of Governmental Industrial Hygienists)**

A2 - Suspected Human Carcinogen

**Reproductive toxicity** No information available.

**STOT - single exposure** No information available.

**STOT - repeated exposure** No information available.

**Target organ effects** Respiratory system, Eyes, Skin.

**Aspiration hazard** No information available.

**12. Ecological information**

**Ecotoxicity**

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	-	LC50: >5000mg/L (96h, Oncorhynchus mykiss)	-	EC50: >1000mg/L (48h, Daphnia magna)

**Persistence and degradability** No information available.

<b>Bioaccumulation</b>	There is no data for this product.
<b>Mobility in soil</b>	No information available.
<b>Other adverse effects</b>	No information available.

**13. Disposal considerations**

Disposal methods

<b>Waste from residues/unused products</b>	Dispose of waste in accordance with environmental legislation. Dispose of in accordance with local regulations.
<b>Contaminated packaging</b>	Do not reuse empty containers.

**14. Transport information**

<u>DOT</u>	Not regulated
------------	---------------

**15. Regulatory information**

Safety, health and environmental regulations/legislation specific for the substance or mixture

International Regulations

**The Montreal Protocol on Substances that Deplete the Ozone Layer** Not applicable

**The Stockholm Convention on Persistent Organic Pollutants** Not applicable

**The Rotterdam Convention** Not applicable

International Inventories

<b>TSCA</b>	Contact supplier for inventory compliance status.
<b>DSL/NDSL</b>	Contact supplier for inventory compliance status.
<b>EINECS/ELINCS</b>	Contact supplier for inventory compliance status.
<b>ENCS</b>	Contact supplier for inventory compliance status.
<b>IECSC</b>	Contact supplier for inventory compliance status.
<b>KECL</b>	Contact supplier for inventory compliance status.
<b>PICCS</b>	Contact supplier for inventory compliance status.
<b>AIIC</b>	Contact supplier for inventory compliance status.
<b>NZIoC</b>	Contact supplier for inventory compliance status.

**Legend:**

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**EINECS/ELINCS** - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances  
**ENCS** - Japan Existing and New Chemical Substances  
**IECSC** - China Inventory of Existing Chemical Substances  
**KECL** - Korean Existing and Evaluated Chemical Substances  
**PICCS** - Philippines Inventory of Chemicals and Chemical Substances  
**AIIC** - Australian Inventory of Industrial Chemicals  
**NZIoC** - New Zealand Inventory of Chemicals

**US Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

**SARA 311/312 Hazard Categories**

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know Regulations**

Chemical name	New Jersey	Massachusetts	Pennsylvania
Lubricating oils (petroleum), C20-50 hydrotreated neutral oil-based 72623-87-1	X	X	X

**U.S. EPA Label Information**

**EPA Pesticide Registration Number** Not applicable

**16. Other information**

**NFPA** Health hazards 2 Flammability 1 Instability 0 Special hazards -  
**HMIS** Health hazards 2 Flammability 1 Physical hazards 0 Personal protection X

**Key or legend to abbreviations and acronyms used in the safety data sheet**

Legend Section 8: Exposure controls/personal protection

TWA TWA (time-weighted average) STEL STEL (Short Term Exposure Limit)  
 Ceiling Maximum limit value \* Skin designation

**Key literature references and sources for data used to compile the SDS**

Agency for Toxic Substances and Disease Registry (ATSDR)  
 U.S. Environmental Protection Agency ChemView Database  
 European Food Safety Authority (EFSA)  
 EPA (Environmental Protection Agency)



Acute Exposure Guideline Level(s) (AEGl(s))  
U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act  
U.S. Environmental Protection Agency High Production Volume Chemicals  
Food Research Journal  
Hazardous Substance Database  
International Uniform Chemical Information Database (IUCLID)  
National Institute of Technology and Evaluation (NITE)  
Australia National Industrial Chemicals Notification and Assessment Scheme (NICNAS)  
NIOSH (National Institute for Occupational Safety and Health)  
National Library of Medicine's ChemID Plus (NLM CIP)  
National Library of Medicine's PubMed database (NLM PUBMED)  
National Toxicology Program (NTP)  
New Zealand's Chemical Classification and Information Database (CCID)  
Organization for Economic Co-operation and Development Environment, Health, and Safety Publications  
Organization for Economic Co-operation and Development High Production Volume Chemicals Program  
Organization for Economic Co-operation and Development Screening Information Data Set  
World Health Organization

**Revision date** 11/30/2022

**Revision Note** No information available.

**Disclaimer**

**The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.**

**End of Safety Data Sheet**