Sealed Lead-Acid Battery

Absorbant Glass Mat (AGM) technology for superior performance. Valve regulated, spill proof construction allows safe operation in any position. Approved for transport by air. D.O.T., I.A.T.A., F.A.A. and C.A.B. certified. U.L. recognized under file number MH 20567.

Specificatio	on						
Nominal Volt	age			12 volts			
Nominal Cap	acity			77º F (25º C)			
20-hr. (0	.25A)			5.00 Ah			
10-hr. (0	.46A)			4.65 Ah			
5-hr. (0	.85A)			4.25 Ah			
1-hr. (3	.00A)			3.00 Ah			
Approximate	Weight			3.09 lbs (1.4 kgs)			
Internal Resi	stance (approx	x.)	32mΩ				
Shelf Life (%	of normal capa	acity at 68	° F (20° C)				
3 Mon	ths	6 Mont	12 Months				
91%		83%	64%				
Temperature	Dependancy	of Capac	city (20 hour rate)				
104° F (40°0	C) 77°F (2	25°C)	32° F (0°C)	5°F (-15°C)			
102%	100%		85%	65%			
AGM Operati	ional Temper	ature					
Charge			32°F to 104°F (0°C to 40°C)				
Discharge	Discharge			5°F to 113°F(-15°C to 45°C)			
AGM Storage	e Temperatur	e	5°F to 104°F (-15°C to 40°C)				




Due to continuous improvements to our products, product may vary slightly from depiction.

Charge Method (Constan	it Voltage)
Cycle Use (Repeating Use	:)
Initial Current	1.5 A or smaller
Control Voltage	14.6 - 14.8 V
Float Use	
Control Voltage	13.6 - 13.8 V


OWERED[®]



Terminals



Discharge Characteristics



www.upgi.com



All specifications subject to change without notice.

IV

4 6 810

(Hour)

0.1CA 0.05CA

20 40

 \setminus

0.250

2

Maintenance-Free

25

JB1

UPG No. D5777

AGM Storage Temperature


L: 3.54 in (90.0 mm) W: 2.76 in (70.1 mm) H: 3.98 in (101 mm) **TH:** 4.21 in (107 mm) Tolerances are +/- 0.04 in. (+/- 1mm) and +/- 0.08 in. (+/- 2mm) for height dimensions. All data subject to change without notice.

Discharge Time vs. Discharge Current


-30 20 15 10 (Hour) 5 4 Duration of Discharge З 2 -1 50 40 30 (Minute) 20 10 5 3 L 0.01 0.05 0.1 ÷ Discharge Current = CA X Nominal Capacity


488 S. Royal Lane Coppell, Texas 75019 P 469.892.1122 T 866.892.1122 F 469.892.1123 sales@upgi.com





Open Circuit Voltage vs Residual Capacity





Charge Current & Final Discharge Voltage

Application	Charge Voltage(V/Cell)		Max.Charge Current		Final Discharge	1 75	1 70	1.60	1 20	
	Temperature	Set Point	Allowable Range	Max.charge Current		Voltage V/Cell	1.75	1.70	1.60	1.30
Cycle Use	25° C(77 °F)	2.45	2.40~2.50	0.3C] [Discharge	0.2C>(A)	0.2C<(A)<0.5C	0.5C<(A)<1.0C	(A)>1.0C
Standby	25℃(77°F)	2.30	2.27~2.3			Current(A)				





Let UPG Power Your Life

www.upgi.com