



# Blue Wolf Ultra Purple Cleaner & Degreaser

1 Gallon BW-P





# Safety Data Sheet (SDS) Blue Wolf Ultra Purple All Purpose Cleaner and Degreaser (BW-P)

SDS Revision  
Date: 02/19/2021

## 1. Identification

### 1.1. Product identifier

#### Product Identity

Blue Wolf Ultra Purple All Purpose Cleaner and Degreaser (BW-P)

#### SDS Number

BWPSDS-01

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### Intended use

Water-based all-purpose cleaner.

### 1.3. Details of the supplier of the safety data sheet

#### Company Name

Blue Wolf Sales and Service  
219 Industrial Park Road  
Bluefield, Virginia 24605

#### Emergency

#### CHEMTREC (USA)

(800) 424-9300

#### Customer Service: Blue Wolf Sales and Service

855-803-1417

## 2. Hazard(s) identification

### 2.1. Classification of the substance or mixture

Skin Corr. 1A;H314

Causes severe skin burns and eye damage.

Eye Dam. 1;H318

Causes serious eye damage.

### 2.2. Label elements



**Danger**

H314 Causes severe skin burns and eye damage.

H318 Causes serious eye damage.

#### [Prevention]:

P260 Do not breathe dust, fume, mist, vapors or spray.

P264 Wash thoroughly after handling.

P280 Wear protective gloves, eye protection, face protection.

#### [Response]:

P301+310 IF SWALLOWED: Immediately call a POISON CENTER, doctor or physician.

P303+361+353 IF ON SKIN (or hair): Remove, take off immediately all contaminated clothing. Rinse skin with water, shower.

P304+340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P305+351+338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses if present and easy to do - continue rinsing.

P310 Immediately call a POISON CENTER, doctor or physician.

P363 Wash contaminated clothing before reuse.



# Safety Data Sheet (SDS) Blue Wolf Ultra Purple All Purpose Cleaner and Degreaser (BW-P)

SDS Revision  
Date: 02/19/2021

**[Storage]:**

P405 Store locked up.

**[Disposal]:**

No GHS disposal statements

## 3. Composition/information on ingredients

This product contains the following substances that present a hazard within the meaning of the relevant State and Federal Hazardous Substances regulations.

Ingredient/Chemical Designations	Weight %	GHS Classification	Notes
2-Butoxy-ethanol CAS Number: 0000111-76-2	5 - 10	Acute Tox. 4;H332 Acute Tox. 4;H312 Acute Tox. 4;H302 Eye Irrit. 2;H319 Skin Irrit. 2;H315	----
Nonylphenol polyethylene glycol ether CAS Number: 0127087-87-0	1 - 5	Eye Dam. 1;H318 Acute Tox. 4;H302 Skin Irrit. 2;H315	----
Sodium hydroxide CAS Number: 0001310-73-2	1 - 5	Skin Corr. 1A;H314 C ≥ 5 % Skin Corr. 1B;H314: 2 % ≤ C < 5 % Skin Irrit. 2;H315: 0,5 % ≤ C < 2 % Eye Irrit. 2;H319: 0,5 % ≤ C < 2 % Met. Corr. 1;H290	----

In accordance with paragraph (i) of §1910.1200, the specific chemical identity and/or exact percentage (concentration) of composition has been withheld as a trade secret.

\*PBT/vPvB - PBT-substance or vPvB-substance.

The full texts of the phrases are shown in Section 16.

## Section 4. First aid measures

### 4.1. Description of first aid measures

**General**

In all cases of doubt, or when symptoms persist, seek medical attention.  
Never give anything by mouth to an unconscious person.

**Inhalation**

Remove to fresh air, keep patient warm and at rest. If breathing is irregular or stopped, give artificial respiration. If unconscious, place in the recovery position and obtain immediate medical attention. Give nothing by mouth.

**Eyes**

Irrigate copiously with clean water for at least 15 minutes, holding the eyelids apart and seek medical attention.

**Skin**

Remove contaminated clothing. Wash skin thoroughly with soap and water or use a recognized skin cleanser.

**Ingestion**

If swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting.

### 4.2. Most important symptoms and effects, both acute and delayed

**Overview**

No specific symptom data available.  
Treat symptomatically. Check section 2.2 (GHS Label Elements) for further details.

**Eyes**

Causes serious eye damage.

**Skin**

Causes severe skin burns.



**Safety Data Sheet (SDS)**  
**Blue Wolf Ultra Purple All Purpose**  
**Cleaner and Degreaser (BW-P)**

SDS Revision  
Date: 02/19/2021

## Section 5. Fire-fighting measures

### 5.1. Extinguishing media

Recommended extinguishing media; alcohol resistant foam, CO<sub>2</sub>, powder, water spray.  
Unsuitable extinguishing media: Do not use; water jet.

### 5.2. Special hazards arising from the substance or mixture

Hazardous decomposition: Explosive hydrogen gas can be liberated on contact with metals, such as zinc, tin or aluminum. Hydrogen gas can result in explosive hazards in confined spaces.

### 5.3. Advice for fire-fighters

As with all fires, wear positive pressure, self-contained breathing apparatus, (SCBA) with a full face piece and protective clothing. Persons without respiratory protection should leave area. Wear SCBA during clean-up immediately after fire. No smoking.

ERG Guide No. ---

## Section 6. Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Put on appropriate personal protective equipment (see section 8).

### 6.2. Environmental precautions

Do not allow spills to enter drains or waterways.

Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

### 6.3. Methods and material for containment and cleaning up

Stop the leak, if possible. Ventilate the space involved. Contain, vacuum up, place in non-sparking container for disposal. Prevent waterway contamination. Construct a dike to prevent spreading. Collect run-off and transfer to drums or tanks for later disposal. Consult a regulatory specialist to determine appropriate state or local reporting requirements, for assistance in waste characterization and/or hazardous waste disposal and other requirements listed in pertinent environmental permits.

## Section 7. Handling and storage

### 7.1. Precautions for safe handling

Handle containers carefully to prevent damage and spillage.

Do not get in eyes, or skin or on clothing. Do not breathe mist. Keep container closed. Use only with adequate ventilation. Do not taste or swallow. Wash thoroughly after handling. To avoid rapid temperature rise, violent spattering, or explosive eruptions always add caustic to water when mixing.

Never add water to a caustic when mixing. Heat water to 80-100 F before adding product. Add small amounts of product slowly and evenly over single addition, Water should not exceed 160° F during addition.

Check section 2.2 (GHS Label Elements) for further details. - [Prevention]:

### 7.2. Conditions for safe storage, including any incompatibilities

Do NOT store near strong acids.

Incompatible materials: Any acidic material, ammonia, urea, oxidizable materials and metals such as nickel, copper, tin, aluminum and iron.

Check section 2.2 (GHS Label Elements) for further details. - [Storage]:

### 7.3. Specific end use(s)

No data available.



**Safety Data Sheet (SDS)**  
**Blue Wolf Ultra Purple All Purpose**  
**Cleaner and Degreaser (BW-P)**

SDS Revision  
 Date: 02/19/2021

**Section 8. Exposure controls / personal protection**

**8.1. Control parameters**

CAS No.	Ingredient	Exposure	
		Source	Value
0000111-76-2	2-Butoxy-ethanol	OSHA	TWA 50 ppm (240 mg/m3) [skin]
		ACGIH	TWA: 20 ppm
		NIOSH	TWA 5 ppm (24 mg/m3) [skin]
0001310-73-2	Sodium hydroxide	OSHA	TWA 2 mg/m3
		ACGIH	Ceiling: 2 mg/m3
		NIOSH	C 2 mg/m3
0127087-87-0	Nonylphenol polyethylene glycol ether	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit

**8.2. Exposure controls**

- Respiratory** Use NIOSH/MSHA approved respirator, following manufacturer's recommendations when concentrations exceed permissible exposure limits.
- Eyes** Wear safety glasses with side shields to protect the eyes. An eye wash station is suggested as a good workplace practice.
- Skin** Chemical resistant clothing such as coveralls/apron and boots should be worn. Chemical impervious gloves required.
- Engineering Controls** Provide adequate ventilation. Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and any vapor below occupational exposure limits suitable respiratory protection must be worn.
- Other Work Practices** Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.
- Check section 2.2 (GHS Label Elements) for further details.

**Section 9. Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

- |   |  |
|---|--|
| <b>Appearance</b>                                   | Color: Purple Physical State: Liquid   |
| <b>Odor</b>   | Slight butyl odor.   |
| <b>Odor threshold</b>                               | Not determined   |
| <b>pH</b>   | 12.50  |
| <b>Melting point / freezing point</b>               | Not Measured   |
| <b>Initial boiling point and boiling range</b>      | Not Measured   |
| <b>Flash Point</b>                                  | > 200 F  |
| <b>Evaporation rate (Ether = 1)</b>                 | Not Measured   |
| <b>Flammability (solid, gas)</b>                    | Not Applicable   |
| <b>Upper/lower flammability or explosive limits</b> | <b>Lower Explosive Limit:</b> Not Measured<br><b>Upper Explosive Limit:</b> Not Measured |



# Safety Data Sheet (SDS)

## Blue Wolf Ultra Purple All Purpose Cleaner and Degreaser (BW-P)

SDS Revision  
Date: 02/19/2021

<b>Vapor pressure (Pa)</b>	Not Measured
<b>Vapor Density</b>	< 1
<b>Relative Density</b>	Not Measured
<b>Solubility in Water</b>	Complete in Water
<b>Partition coefficient n-octanol/water (Log Kow)</b>	Not Measured
<b>Auto-ignition temperature</b>	Not Measured
<b>Decomposition temperature</b>	Not Measured
<b>Viscosity (cSt)</b>	Not Measured

**9.2. Other information**

No other relevant information.

### Section 10. Stability and reactivity

**10.1. Reactivity**

Hazardous Polymerization will not occur.

**10.2. Chemical stability**

Stable under normal circumstances.

**10.3. Possibility of hazardous reactions**

No data available.

**10.4. Conditions to avoid**

Avoid strong acids, metals and organic material such as chlorinated hydrocarbons.

**10.5. Incompatible materials**

Any acidic material, ammonia, urea, oxidizable materials and metals such as nickel, copper, tin, aluminum and iron.

**10.6. Hazardous decomposition products**

Explosive hydrogen gas can be liberated on contact with metals, such as zinc, tin or aluminum. Hydrogen gas can result in explosive hazards in confined spaces.

### Section 11. Toxicological information

**Acute toxicity**

2-butoxyethanol and its acetate are readily absorbed through the skin and will cause harmful effects on the blood.

Note: When no route specific LD50 data is available for an acute toxin, the converted acute toxicity point estimate was used in the calculation of the product's ATE (Acute Toxicity Estimate).

Ingredient	Oral LD50, mg/kg	Skin LD50, mg/kg	Inhalation Vapor LC50, mg/L/4hr	Inhalation Dust/Mist LC50, mg/L/4hr	Inhalation Gas LC50, ppm
2-Butoxy-ethanol - (111-76-2)	1,414.00, Guinea Pig - Category: 4	1,200.00, Guinea Pig - Category: 4	No data available	No data available	No data available
Nonylphenol polyethylene glycol ether - (127087-87-0)	No data available	No data available	No data available	No data available	No data available
Sodium hydroxide - (1310-73-2)	No data available	No data available	No data available	No data available	No data available

**Carcinogen Data**

CAS No.	Ingredient	Source	Value



## Safety Data Sheet (SDS) Blue Wolf Ultra Purple All Purpose Cleaner and Degreaser (BW-P)

SDS Revision  
Date: 02/19/2021

0000111-76-2	2-Butoxy-ethanol	OSHA	Regulated Carcinogen: No
		NTP	Known: No; Suspected: No
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: Yes; Group 4: No;
		ACGIH	A3
0001310-73-2	Sodium hydroxide	OSHA	Regulated Carcinogen: No
		NTP	Known: No; Suspected: No
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No;
		ACGIH	No Established Limit
0127087-87-0	Nonylphenol polyethylene glycol ether	OSHA	Regulated Carcinogen: No
		NTP	Known: No; Suspected: No
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No;
		ACGIH	No Established Limit

Classification	Category	Hazard Description
Acute toxicity (oral)	---	Not Applicable
Acute toxicity (dermal)	---	Not Applicable
Acute toxicity (inhalation)	---	Not Applicable
Skin corrosion/irritation	1A	Causes severe skin burns and eye damage.
Serious eye damage/irritation	1	Causes serious eye damage.
Respiratory sensitization	---	Not Applicable
Skin sensitization	---	Not Applicable
Germ cell mutagenicity	---	Not Applicable
Carcinogenicity	---	Not Applicable
Reproductive toxicity	---	Not Applicable
STOT-single exposure	---	Not Applicable
STOT-repeated exposure	---	Not Applicable
Aspiration hazard	---	Not Applicable

### Section 12. Ecological information

#### 12.1. Toxicity

No additional information provided for this product. See Section 3 for chemical specific data.

#### Aquatic Ecotoxicity

Ingredient	96 hr LC50 fish, mg/l	48 hr EC50 crustacea, mg/l	ErC50 algae, mg/l
2-Butoxy-ethanol - (111-76-2)	1,474.00, Oncorhynchus mykiss	1,550.00, Daphnia magna	1,840.00 (72 hr), Pseudokirchneriella subcapitata
Nonylphenol polyethylene glycol ether - (127087-87-0)	Not Available	Not Available	Not Available
Sodium hydroxide - (1310-73-2)	125.00, Gambusia affinia	40.40, Ceriodaphnia sp.	Not Available

#### 12.2. Persistence and degradability

There is no data available on the preparation itself.

#### 12.3. Bioaccumulative potential

Not Measured

#### 12.4. Mobility in soil

No data available.



# Safety Data Sheet (SDS) Blue Wolf Ultra Purple All Purpose Cleaner and Degreaser (BW-P)

SDS Revision  
Date: 02/19/2021

## 12.5. Results of PBT and vPvB assessment

This product contains no PBT/vPvB chemicals.

## 12.6. Other adverse effects

No data available.

## Section 13. Disposal considerations

### 13.1. Waste treatment methods

Observe all federal, state and local regulations when disposing of this substance.

## Section 14. Transport information

Domestic Ground Shipments less than 5 liters (1.3 gallon): This product is not considered a Corrosive Hazard, excepted 173.154 (b)(2).

	<b>DOT (Domestic Surface Transportation)</b>	<b>IMO / IMDG (Ocean Transportation)</b>	<b>ICAO/IATA</b>
<b>14.1. UN number</b>	UN1760	UN1760	UN1760
<b>14.2. UN proper shipping name</b>	UN1760, Corrosive liquids, n.o.s., (Sodium Hydroxide), 8, III	UN1760, Corrosive liquids, n.o.s., (Sodium Hydroxide)	UN1760, Corrosive liquids, n.o.s., (Sodium Hydroxide)
<b>14.3. Transport hazard class(es)</b>	<b>DOT Hazard Class:</b> 8 <b>Sub Class:</b> Not Applicable	<b>IMDG:</b> 8 <b>Sub Class:</b> Not Applicable	<b>Air Class:</b> 8 <b>Sub Class:</b> Not Applicable
<b>14.4. Packing group</b>	III	III	III
<b>14.5. Environmental hazards</b>			
<b>IMDG</b>	Marine Pollutant: No;		
<b>14.6. Special precautions for user</b>	Not Applicable		

## Section 15. Regulatory information

<b>Regulatory Overview</b>	The regulatory data in Section 15 is not intended to be all-inclusive, only selected regulations are represented.
<b>Toxic Substance Control Act (TSCA)</b>	All components of this material are either listed or exempt from listing on the TSCA Inventory.
<b>EPCRA 302 Extremely Hazardous:</b>	To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.
<b>EPCRA 313 Toxic Chemicals:</b>	
	2-Butoxy-ethanol
<b>Proposition 65 - Carcinogens (&gt;0.0%):</b>	To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.
<b>Proposition 65 - Developmental Toxins (&gt;0.0%):</b>	To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.





**Safety Data Sheet (SDS)**  
**Blue Wolf Ultra Purple All Purpose**  
**Cleaner and Degreaser (BW-P)**

SDS Revision  
Date: 02/19/2021

**Proposition 65 - Female Repro Toxins (>0.0%):**

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

**Proposition 65 - Male Repro Toxins (>0.0%):**

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

**Proposition 65 Label Warning:**

This product contains no chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

**Section 16. Other information**

**SDS Revision Date** 02/19/2021

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. We accept no responsibility and disclaim all liability for any harmful effects which may be caused by exposure to our products. Customers/users of this product must comply with all applicable health and safety laws, regulations, and orders.

The full text of the phrases appearing in section 3 is:

H290 May be corrosive to metals.

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

End of Document