
ADJUSTABLE STEEL GANTRY CRANE - AHS-2-20-14

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS AHS-2-20-14 CAPACITY IS 2,000 LBS.

BASE WIDTH IS 88 1/2"

MAX OVERALL HEIGHT IS 178 1/8"

I-BEAM HEIGHT IS 10 1/8"

I-BEAM FLANGE WIDTH IS 4"

OVERALL I-BEAM LENGTH IS 239 3/4"

USABLE I-BEAM LENGTH IS 209 3/4"

ADJUSTABLE UNDER I-BEAM HEIGHT

168" MAX

102" MIN

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS CASTERS: (4) Ø8" X 2" WIDE GLASS FILLED

NYLON ŚWIVEL CASTERS WITH FOUR **LOCKING POSITIONS**

SPECIAL FEATURES NONE

		DIMENSION TOLERANCE ± 1/4"				
	APPROVA	I, THE UNDERSIGNED, AGREE THAT THE F REPRESENTED SATISFIES DESIGN AND I REQUIREMENTS. I ALSO ACKNOWLEDGE CONFIRM PRODUCT AND INSTALL COMPLIANCE WITH ALL APPLICABLE FE AND LOCAL REGULATIONS AND STA UNITS REQUIRING APPROVAL DI MODIFIED ARE NON-RETUI [] As drawn [] As n				IMENSION MY DUTY TO ATION DERAL, STATE NDARDS. RAWINGS OR
	L	Signed:_				_Date:
		Printed Name: LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING				
	DISTRIBUTOR'S NAME:					P.O.# X
VESTIL MANUFACTURING					W.O.# X	
DRAWN BY: ND			DATE: 10/01/09		SALES: X	
REFERENCE: X QUOTED LEAD TIME: X QUOTE # X					FILE NAME: 28-007-072	