

DATA SHEET



5-Port USB Wall Charger - AC to USB Adapter, 5V 8A Output

Simultaneously charge five mobile devices from a single outlet

OVERVIEW

The 5-Port USB Wall Charger - AC to USB Adapter is an ideal solution for charging or powering portable devices at home, in the office, or on the go. This adapter features a compact design for easy portability and provides a total maximum power output of 5V and 8A for device charging. The compact design of this adapter makes it easy to toss into a suitcase or backpack for charging on the go.

Five USB-A ports provide 5 volts and 2.4 amps, with a max output of 8 amps of power for device charging from this adapter when it is plugged into an AC outlet. The power output makes this adapter the perfect solution for charging smartphones and tablets.

FEATURES

- 5V, 8A total maximum output
- 5 standard USB-A ports
- 5V, 2.4A maximum output for each port
- Compact size

ITEM DESCRIPTION

20278 5-Port USB Wall Charger - AC to USB Adapter, 5V 8A Output

DATA SHEET

SPECIFICATIONS:


5-Port USB Wall Charger - AC to USB Adapter, 5V 8A Output

ELECTRICAL SPECIFICATIONS:

- Input voltage range: 90-264V/AC
- Nominal input voltage: 100-240V/AC
- Frequency range: 47-63Hz
- Input current with full load: $\leq 1.5A$
- Inrush current: $\leq 100A$
- Efficiency (USB Port): $\geq 86.07\%$
- Standby Power Loss: $\leq 0.1W$
- Output Port: USB-A- 1-USB5
- Output Voltage: 5.0V
- Output ID Voltage: D+2.7V/D-:2.7V
- Output Rated Current: 2.4A
- Output Port ID: Smart ID

PHYSICAL SPECIFICATIONS:

- Operating Temperature: Operating: $-10^{\circ}C$ to $+35^{\circ}C$
- Operating Storage: Storage: $-20^{\circ}C$ to $+75^{\circ}C$
- Operating Humidity: From 20% to 80% relative humidity (non-condensing)
- Storage Humidity: From 10% to 90% relative humidity (non-condensing)
- Operating Altitude: Up to 2000m
- Storage Altitude: Up to 2000m



C2G[®]
A brand of **legrand**

6500 Poe Ave.
Dayton, OH 45414
Phone: 800.CABL.911
www.c2g.com

Follow Us

