
APPROX WEIGHT: 41.44 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



ENG. FAB. **POWER**

STANDARD FEATURES

MODEL NUMBER: AHT-L-1936

CAPACITY: 500 LBS. DECK WIDTH: 19" **DECK LENGTH: 36"** RAISED HEIGHT: 8 3/4"

LOWERED HEIGHT: 6 3/4" ALL STEEL CONSTRUCTION

(ASTM A-36 MIN.) WITH WELDING TO MEET AWS.

ERGO MATTING IS BLUE TOUGH BAKED IN POWDER COATED YELLOW FINISH

SPECIAL FEATURES

NONE

		DIN	MENSION TOLE	RANCE ± 1/4	ļ"	
EATURES	A P P R O	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. ANY MODIFIED UNITS ARE NON-RETURNABLE				
	V	L] As drawn	[] As m	narked	
	A	Signed:			Date:	
	L	Printed Name:				
		LEAD TIME WILL S	TART UPON RECE	IPT OF SIGNED	APPROVAL DRAWII	٧G
FOR INTERNAL USE	CIVEI	BUTOR'S NAME:			P.O.# X	
PROJECT SIGN (V	VESTIL MANUFACTURING DRAWN BY: MTS DATE: 12/27/13			W.O.# X	_
ENG.	DRAW				SALES: X	_
FAB.	REFER	ENCE: X	12,	SCALE: 1:8	FILE NAME:	_
POWER	QUOT	ED LEAD TIME: 🗸	QUOTE #	00/ (EE. 1.0	14-007-197	

Χ