

# COUNTER BALANCED SINGLE DRUM STACKER - DRLT-CB-54-MDPL

\*\*\*ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE\*\*\*

APPROX WEIGHT: 820 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!



ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

DIMENSION TOLERANCE  $\pm 1/2"$

## STANDARD FEATURES

- MODEL NO: DRLT-CB-54-MDPL
- OVERALL LENGTH IS: 52"
- OVERALL WIDTH IS: 26"
- OVERALL HEIGHT IS: 58"
- RAISED HEIGHT IS: 54"
- LOWERED HEIGHT IS: 26 3/4"
- MAXIMUM UNIFORM CAPACITY IS: 700 LBS
- WORKS WITH MOST STYLES 30, 55, OR 85 GALLON POLY OR STEEL DRUMS
- MANUAL DRIVE POWERED LIFT
- 12V POWERED LIFT / MANUAL DRIVE
- (2) 8" x 3" SWIVEL CASTERS
- (2) 6" x 3" RIGID CASTERS
- TOUGH BAKED IN POWDER COATED BLACK AND YELLOW FINISH

## SPECIAL FEATURES

NONE

<b>A P P R O V A L</b>	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.	
	<b>UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE</b>	
	[ ] As drawn      [ ] As marked	
Signed: _____		Date: _____
Printed Name: _____		
<b>LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING</b>		

DISTRIBUTOR'S NAME:		P.O.#
<b>VESTIL MANUFACTURING</b>		X
DRAWN BY: TM		W.O.#
DATE: 02/24/2021		X
REFERENCE: X		SALES: X
SCALE: NTS		FILE NAME:
QUOTED LEAD TIME: X		DRLT-CB-54-MDPL
QUOTE #		X