
APPROX WEIGHT: 20.72 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON






MODEL NUMBER IS DRUM-DP-LD-30-BU
OVERALL DIAMETER IS Ø 19 3/4"
INNER DIAMETER IS Ø 19 1/8"
OVERALL HEIGHT IS 8 7/16"
MAX CAPACITY IS 300 LBS
MADE FROM HIGH-DENSITY POLYETHYLENE
HARD RUBBER CASTERS
COLOR IS SAFETY BLUE, MUNSELL - 2.5PB 3.5/10
WORKS WITH 30 GALLON DRUMS AND 5 GALLON BUCKETS

SPECIAL FEATURES

NONE



DIMENSION TOLERANCE ± 1/4"

		DIMILINO	ION TOLLINANCE ± 1/4
APPROV	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked		
A	Signed:		Date:
L	Printed Name: LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING		
DISTRI	BUTOR'S NAME:	P.O.# X	
	ESTIL MANUF	W.O.# X	
DRAV	^{VN BY:} KGH	DATE: 8/24/201	6 SALES: X
REFER	ENCE: X	:: 1:8 FILE NAME:	
QUOT	TED LEAD TIME: X	QUOTE #	31-007-254-001