

## DRUM DOLLY - DRUM-DP-LD-55-BK

APPROX WEIGHT: 22.82 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON.






## STANDARD FEATURES

MODEL NUMBER IS DRUM-DP-LD-55-BK OVERALL DIAMETER IS \$\psi 24 1/4"\$ INNER DIAMETER IS Ø 23 5/8" **OVERALL HEIGHT IS 8 5/16"** MAX CAPACITY IS 300 LBS MADE FROM HIGH DENSITY POLYETHYLENE HARD RUBBER 3" CASTERS **COLOR IS BLACK** WORKS WITH 55 OR 30 GALLON DRUMS

## SPECIAL FEATURES

NONE



DIMENSION TOLERANCE ± 1/4			
APPROV	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.  UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE  [ ] As drawn [ ] As marked		
Ā	Signed:		Date:
┞┖	Printed Name:  LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING		
DISTRIBUTOR'S NAME:			P.O.# X
VESTIL MANUFACTURING W.O.# X			
DRAWN BY: KGH		DATE: 8/24/2016	SALES: X
REFERENCE: X SCALE: 1:12 FILE NAME:			
QUOI	TED LEAD TIME: 🗸	QUOTE #	31-007-255