




MODEL NAME - PAIL-LINE

APPROX WEIGHT: 0.31 lbs.
 DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE



DIMENSION TOLERANCE $\pm 1/4"$

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

STANDARD FEATURES

MODEL NUMBER IS PAIL-LINE
 DIAMETER(EXCLUDING TOP LIP) IS $\varnothing 11 \frac{1}{4}"$
 DIAMETER(INCLUDING TOP LIP) IS $\varnothing 12 \frac{3}{4}"$
 OVERALL HEIGHT IS $13 \frac{1}{4}"$
 MAX CAPACITY IS 5 GAL.
 VACUUM FORMED SEAMLESS CONSTRUCTION
 LINER AVERAGE THICKNESS IS 0.381MM
 LINER SURFACE IS TEXTURED/ROUGH
 LINER COMPOSITION : TRANSLUCENT
 SEMI-RIGID POLYETHYLENE (HDPE)

SPECIAL FEATURES

NONE

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

ALL SPECIAL UNITS ARE NON-RETURNABLE

As drawn As marked

Signed: _____ Date: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
DRAWN BY: DEY		DATE: 12/14/11
DATE: 12/14/11		SALES: X
REFERENCE: X	SCALE: 1:8	FILE NAME:
QUOTED LEAD TIME: X	QUOTE # X	30-007-880