
## OPTIONAL CASTER KIT FOR PS-4045 - PS-RF-CK

PROX WEIGHT: 56.87 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



## STANDARD FEATURES

MODEL NUMBER: PS-RF-CK OVERALL WIDTH: 6 15/16"

OVERALL LENGTH (INCLUDING CASTERS): 48 13/16"

USABLE LENGTH: 45 3/4"

OVERALL HEIGHT (INCLUDING CARRIAGE BOLT): 9 1/16"

USABLE HEIGHT:7 7/8" MAX CAPACITY: 1500 LBS

TOUGH BAKED IN POWDER COATED YELLOW FINISH

6" X 2" GLASS FILLED NYLON CASTERS

(2) SWIVEL W/ BRAKE

(2) RIGID

INCLUDES MOUNTING HARDWARE

## SPECIAL FEATURES

NONE

	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION
<b>A</b>	REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION
2	COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
3	AND LOCAL REGULATIONS AND STANDARDS.
<b>~</b> I	UNITS REQUIRING APPROVAL DRAWINGS (

## UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [ ] As drawn [ ] As marked

Signed: Date:

Printed Name:\_

	1 1	Tilliou Haillo:						
		LEAD TIME WILL	APPROVAL DRAWIN					
[	DISTRI					P.O.# <b>X</b>		
		ESTIL MAN	IG	W.O.# X				
[	DRAW	<sup>/N BY:</sup> TAW		DATE: 2/1	1/2016	SALES: X		
I	REFER	ENCE: X		•	SCALE: 1:12	FILE NAME:		
(	QUOT	ED LEAD TIME: X		QUOTE #		15-007-146		