
SINGLE SCISSOR LIFT & TILT TABLE - UNI-5448-6

APPROX WEIGHT: 952.67 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACK

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS: UNI-5448-6

CAPACITY: 6,000 LBS. EVENLY DISTIBUTED SEQUENCE 1:

PAISED H

RAISED HEIGHT: 14 3/4", TILT ANGLE 35° OVERALL HEIGHT: 42"

SEQUENCE 2:

RAISED HEIGHT 11 3/4", TILT ANGLE: 40°

OVERALL HEIGHT 42 1/4" LEVEL HEIGHT: 8"

DECK SIZE: 54" W X 48" L WITH 12" LIP

INTEGRAL MAINTENCE LOCK

ADJUSTABLE UPWARD TRAVEL LIMIT SWITCH UNIT MUST BE LAGGED TO THE FLOOR

DURABLE LIQUID PAINT BLUE FINISH

SPECIAL FEATURES

NONE

PLEASE CIRCLE SPECIFICATIONS **POWER** AC * AIR/OIL * DC MOTOR VOLTAGE 115 208 DEDICATED CIRCUIT REQUIRED MOTOR PHASE SINGLE **THREE** CONTROL **HAND FOOT** ~ ALL BATTERY CHARGERS ARE 115V AC ~ ON-BOARD REMOTE BATTERY CHRO QUOTED LEAD TIME: X * AVAILABLE AT ADDITIONAL COST

DIMENSION TOLERANCE ± 1/4"

03-007-045

•	A P P R O	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. ANY MODIFIED UNITS ARE NON-RETURNABLE		
]	V		As drawn [] As	
	A	Signed:		Date:
		Printed Name:		
DISTRIBUTOR'S NAME:			P.O.# X	
V ESTIL TVIT (1 VOT) (C TOT(11 VO			W.O.# X	
	DRAV	WN BY: X	DATE: XX/XX/XX	SALES: X
-	REFER	RENCE: X	SCALE: 1	:20 FILE NAME:

QUOTE #