
ECONOMY SPREADER BEAM - SBM-40-8

APPROX WEIGHT: 192.92 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS SBM-40-8 **OVERALL WIDTH IS 4 13/16" OVERALL HEIGHT IS 20 9/16" OVERALL LENGTH IS 96"** USABLE BAIL IS 3"x5" MINIMUM SPREAD IS 69" MAXIMUM SPREAD IS 93" HEADROOM IS 18 3/8" MAX CAPACITY IS 4000 LBS.

SPECIAL FEATURES

NONE

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. R ANY MODIFIED UNITS ARE NON-RETURNABLE 0

DIMENSION TOLERANCE ± 1/4"

[] As drawn [] As marked

Signed: Printed Name:

Date:

Α

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

| | | DISTRIBUTORIS ALALAS | | | D O !! |
|-----------------------|--|-----------------------------------|---------|------------|----------------|
| FOR INTERNAL USE ONLY | | DISTRIBUTOR'S NAME: | | | P.O.# X |
| PROJECT SIGN OFF | | | | W.O.# | |
| SALES | | | NINOL | 9 | γ X |
| 07 1220 | | DRAWN BY: DFY | DATE: | | SALES: V |
| ENG. | | DEY | 12/1 | //10 | ^ |
| | | REFERENCE: V | C | CALE: 1:12 | FILE NAME: |
| FAB. | | X | 3 | CALE: 1:12 | |
| POWER | | Quoted lead time: $_{\mathbf{Y}}$ | QUOTE # | | 08-007-182 |
| OVVLK | | ^ | X | | |