

MEDIUM DUTY, HIGH PERFORMANCE SEMI-APPROX WEIGHT: 2186 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!! ITOMATIC STRETCH WRAP MACHINE- SWA-82-AW

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE





*115V SUPPLY VOLTAGE; INCLUDES 12' LONG POWER CORD WITH NEMA 5-15 PLUG *10A AT FULL LOAD

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

DIMENSION TOLERANCE ± 1/4"

STANDARD FEATURES MODEL NUMBER IS: SWA-82-AW

CAPACITY IS: 4,000 LBS: OVERALL WIDTH IS: 78 3/4" OVERALL LENGTH IS: 131" OVERALL MAST HEIGHT IS: 92" 78 3/4" DIAMETER TOP PLATE VARIABLE SPEED CONTROL, 0-13 RPM CAN HANDLE FILM ROLLS UP TO 20" LONG WRAPS DOWN TO 3" ABOVE TURNTABLE

APPROXIMATE CRATE SIZE: 84" x 134" x 24" TALL

TOUGH BAKED IN POWDERCOAT BLUE FINISH

AND LOCAL REGULATIONS AND STANDARDS.

UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [] As marked [] As drawn Signed: Printed Name:

P

R O V

A

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS

REPRESENTED SATISFIES DESIGN AND DIMENSION

REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO

CONFIRM PRODUCT AND INSTALLATION

COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE

	WILL START UPON RECEIP.	<u>T OF SIGNED APPROVAL DRAWING</u>
DISTRIBUTOR'S NAME:		P.O.# X
	JFACTURING	W.O.# X
DRAWN BY: TJM	DATE: 11/08/	10 SALES: X
REFERENCE: X	SCA	ALE: NTS FILE NAME:
QUOTED LEAD TIME: X	QUOTE #	20-007-104-003

SPECIAL FEATURES

NONE