


S-2CB-118 (2,000 lbs Counter-Balanced Powered Drive Lift)



Aisle width: 130"

Specifications

Model Number: S-2CB-118
 Capacity (0-62"): 2,000 lbs
 Capacity (62-118"): 1,000 lbs
 Lift Height: 118"
 Lowered Height: 2"
 Drive Motor: 24V/1KW
 Lift Motor: 24V/2KW
 Battery: 2x12V/135Ah
 Battery Charger: 24V/12amp
 Lift Speed w/o Load: 5.9"/sec
 Lift Speed w/load: 2.95"/sec
 Lower down speed w/o load: 4"/sec
 Lower down speed w/load: 3.15"/sec
 Travel Speed w/o load: 3.43 m/h
 Travel speed w/load: 2.8 m/h

VESTIL MANUFACTURING CORP.	
Model:	S-2CB-118
Descrip:	2,000 lbs Counter-Balanced Powered Drive Lift
Design:	T.M
Date:	04/04/2022