


**Product Details for 031 -0061 -0001**



**031 -0061 -0001**

Tyco Part Number: 1467938 - 1

[Active](#)

**SMB RF Connectors**

[Not ELV or RoHS Compliant](#)

**Product Highlights:**

- ? Connector
- ? Jack
- ? Miniature
- ? Terminate To Printed Circuit Board
- ? Coupler Style = Threaded

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [RIGHT ANGLE PRINTED CIRCUIT RECEPTACLE S -50 SERIES](#)  
(PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? Connector Series = Miniature
- ? [Grade](#) = Commercial
- ? Safety Wire Holes = Without
- ? [PCB Mount Angle](#) = Right Angle
- ? Board Standoff = Without
- ? Thread Size = 4.83 [.190] -32 UNF -2A
- ? PCB Mount Style = Thru Hole
- ? Body Material = Brass
- ? Dielectric Material = TEFLON

**Mechanical Attachment:**

- ? [Panel Attachment](#) = Without

**Electrical Characteristics:**

- ? [Connector Impedance \(?\)](#) = 50
- ? Environmental Seal = Without
- ? Solderless = No

**Body Related Features:**

- ? Coupler Style = Threaded
- ? [Pin Protection](#) = Without
- ? Solder Lug = Without
- ? [Body Plating](#) = Silver
- ? Terminal Style = Straight Pin

**Contact Related Features:**

- ? [Center Contact Plating](#) = Gold
- ? Contacts = With

**Configuration Related Features:**

- ? Terminal Length (mm [in]) = 3.94 [0.155]

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C

**Conditions for Usage:**

- ? [Terminate To](#) = Printed Circuit Board

**Other:**

- ? Brand = Microdot