

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0557550819](#)
Status: **Active**
Overview: [MicroTPA Connector System](#)
Description: 2.00mm Pitch MicroTPA Wire-to-Board Header, Vertical, Shrouded, Kinked PC Tail, with Inner Positive Lock, 8 Circuits

Documents:

Drawing (PDF)	Product Specification PS-51216-007-001 (PDF)
3D Model	Packaging Specification SPK-55755-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	55755
Application	Signal, Wire-to-Board
Overview	MicroTPA Connector System
Product Name	MicroTPA
Taxonomy	PCB Headers and Receptacles
UPC	822348802395

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	13.45mm
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	739.727/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[55755 Series](#)

Mates With

[51216 Wire-to-Board and Wire-to-Wire Receptacle Housing](#)

Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 2.5A

Voltage - Maximum 250V

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-55755-001-001

Product Specification PS-51216-007-001

Sales Drawing SD-55755-005-001

This document was generated on 09/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION