

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200062799](#)  
**Status:** **Active**  
**Overview:** [Brad Micro-Change \(M12\) Connectors](#)  
**Description:** Micro-Change (M12) Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 0.34mm<sup>2</sup> PVC Cable, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120006](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Protocol N/A  
 Region Europe  
 Taxonomy Circular Industrial Cordsets  
 Type Single Ended  
 UPC 883906138394

**Physical**

Cable Diameter 5.80mm (.230")  
 Cable Length 1.0m (3.28')  
 Color - Cable Jacket Black  
 Coupling Style Threaded  
 Gender Male-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PUR  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold  
 Net Weight 50.000/g  
 Orientation Straight to Pigtail  
 Poles 5  
 Temperature Range - Operating -30° TO +80°C  
 Wire Size AWG N/A  
 Wire/Cable Type UL 2464

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 805006E03M010

**Reference - Drawing Numbers**

Sales Drawing 1200659185-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000380980\_00\_000.pdf

CER\_4000410293\_00\_000.pdf

**Search Parts in this Series**

[120006 Series](#)

This document was generated on 10/17/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**