

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936050073](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect Hand Crimp Tool for 10A, 16A, and 40A Turned Contacts and Bush Terminals, 0.14-4.00mm<sup>2</sup> (26-12) AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                     |   |
|---------------------|---|
| Product Family      | Industrial Connectors / Enclosures                    |
| Series              | <a href="#">93605</a>                                 |
| Comments            | Crimp tool, Die set, and Locator included.            |
| Function            | Crimp   |
| Level of Automation | Manual  |
| Overview            | <a href="#">GWconnect Heavy Duty Connectors (HDC)</a> |
| Product Category    | Application Tooling                                   |
| Product Name        | GWconnect   |
| Taxonomy            | Crimp Presses and Crimp Hand T                        |
| Tool Type           | Hand Crimp Tool                                       |
| UPC                 | 887191892450  |

**Physical**

|                           |           |
|---------------------------|-----------|
| Net Weight                | 660.000/g |
| Packaging Type            | Carton    |
| Wire Size AWG             | 12-26     |
| Wire Size mm <sup>2</sup> | 0.14-4.00 |

**Material Info**

|                    |             |
|--------------------|-------------|
| Engineering Number | 8500.7925.0 |
|--------------------|-------------|



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of  
Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400780\_00\_000.pdf

**Search Parts in this Series**

[93605 Series](#)

**Use With**

10A, 16A, and 40A Turned Contacts