

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200660380](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (90°), 22 AWG, Yellow TPE Cable, 4.0m (13.12') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120066](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Micro-Change (M12)  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Region America  
 Taxonomy Circular Industrial Cordsets  
 Type Double Ended  
 UPC 78678883346

**Physical**

Cable Diameter 5.30mm (.209")  
 Cable Length 4.0m (13.12')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket TPE  
 Material - Connector Body TPE  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold  
 Net Weight 187.500/g  
 Orientation 90° to Straight  
 Poles 4  
 Temperature Range - Operating -20° to +105°C  
 Wire Size AWG 22  
 Wire/Cable Type PLTC/ITC

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 884031K05M040

**Reference - Drawing Numbers**

Sales Drawing 1200660973-000, SD-120066-024-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000408918\_00\_000.pdf

CER\_4000410292\_00\_000.pdf

**Search Parts in this Series**

[120066 Series](#)

This document was generated on 10/28/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**