

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200790107](#)
Status: **Active**
Overview: Brad Ultra-Lock Connection System
Description: Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
 Series [120079](#)
 Connector End A Ultra-Lock (M12)
 Connector End B Pigtail
 IP Rating IP69K
 Material - Contact Copper Alloy
 Overview [Brad Ultra-Lock Connection System](#)
 Product Name Ultra-Lock (M12)
 Protocol EtherNet
 Region America
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 78678884703

Physical

Cable Diameter 5.33mm (.210")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Yellow
 Coupling Style Push to Lock
 Gender Male-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Net Weight 251.000/g
 Orientation Straight to Pigtail
 Poles 4
 Temperature Range - Operating -25° to +90°C
 Wire Size AWG 22
 Wire/Cable Type UL 2661

Electrical


Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number W04006A09M020

Reference - Drawing Numbers

Sales Drawing SD-120079-024-001



EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)
 Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

Not Relevant

Compliant with Exemption 3

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

Not Contained

CER_4000410036_00_000.pdf

CER_4000410293_00_000.pdf

Search Parts in this Series

120079 Series

This document was generated on 10/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION