

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1203410603](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Teal Shielded PUR Cable, 3.0m (9.84') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-120341-600-001 \(PDF\)](#)

Agency Certification

UL E361772

General

Product Family	Industrial Cordsets
Series	120341
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP20
Material - Contact	Brass
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Industrial Ethernet
Region	America, Asia, Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	887191679044

Physical

Cable Diameter	6.40mm (.252")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	N/A
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	151.300/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40° to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR

Electrical


Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC / 60V DC

Material Info

Engineering Number	E66E06020M030
--------------------	---------------

Reference - Drawing Numbers

Packaging Specification	PK-120341-600-001
-------------------------	-------------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120341](#) Series

Mates With

[120341](#) Micro-Change CAT6A Receptacles

This document was generated on 09/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION