

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300110280](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change B-Size Double-Ended Cordset, 8 Poles, Male (Straight) to Female (Straight), 18/22 AWG, Yellow PVC Cable, 15.0m (49.21') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
 Series [130011](#)
 Connector End A Mini-Change
 Connector End B Mini-Change
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Mini-Change Connectors](#)
 Product Name Mini-Change
 Protocol DeviceNet
 Region America
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78172514373

Physical

Cable Diameter 7.36mm (.290")
 Cable Length 15.0m (49.21')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPE
 Material - Coupling Nut Black Epoxy Coated Zinc
 Material - Plating Mating Gold
 Net Weight 66.660/g
 Orientation Straight to Straight
 Poles 8
 Temperature Range - Operating -20° to +90°C
 Wire Size AWG 18, 22
 Wire/Cable Type AWM 2661

Electrical


Current - Maximum per Contact 2.5A
 Voltage - Maximum 300V

Material Info

Engineering Number 228020A04M150

Reference - Drawing Numbers

Sales Drawing SD-130011-007-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000410038_00_000.pdf

Declaration of Conformity

ZZCERT_UKCA

CER_4000406014_00_000.pdf

- Declaration of Conformity

Search Parts in this Series

[130011 Series](#)

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION