

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300480179](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (90°) to Male (90°), 26 AWG, PVC Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [130048](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Industrial Ethernet Solutions](#)
 Performance Category 5e
 Product Name Micro-Change (M12)
 Protocol N/A
 Region America, Asia, Europe
 Type Double Ended
 UPC 78678803832

Physical

Cable Diameter 5.59mm (.220")
 Cable Length 1.0m (3.28')
 Color - Cable Jacket Teal
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PVC
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Orientation 90° to 90°
 Poles 4
 Temperature Range - Operating -20° to +75°C
 Wire Size AWG 26
 Wire/Cable Type N/A

Electrical


Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V

Material Info

Engineering Number E11A06315M010

Reference - Drawing Numbers

Sales Drawing SD-120108-026-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/01/2017 (12 January 2017)
 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000410041_00_000.pdf

Declaration of

Conformity

ZZCERT_UKCA

CER_4000406115_00_000.pdf

- Declaration of

Conformity

Search Parts in this Series

130048 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION