


MOLEX SAP P/N#	ENGINEERING P/N#	"L" (Meters)	"L" (INCH)	TOLERANCE (INCH)
1300652199	1300652199	5 M	196.85"	+6.50"/-0.00"



SPECIFICATIONS:

COUPLING NUT MATERIAL: ZINC DIECAST WITH BLACK ELECTROPHORETIC COATING
 CONTACT MATERIAL: GOLD/NICKEL OVER COPPER ALLOY
 INSERT MATERIAL: BLACK PVC
 OVERMOLD MATERIAL: FEMALE - GRAY PVC
 MALE - BLACK PVC
 CABLE: #14/4 BLACK PVC
 ASSEMBLY RATING: 600V, 15A
 ENVIRONMENTAL: -20°C TO 90°C
 IP67 WHEN MATED

ELECTRICAL DIAGRAM

1	BLACK	1
2	WHITE	2
3	RED	3
4	GRN/YLW OR GREEN	4

CUSTOMER PRODUCTION APPROVAL
 APPROVED BY: _____
 DATE: _____
 MUST BE SIGNED AND RETURNED BEFORE
 PRODUCTION WILL BEGIN.

RESTRICTED SALES DRAWING

INITIAL RELEASE EC NO: IPG2014-0872 DRWN: VOU 2013/11/12 CHKD: BARDEN APPR: JFMURPHY 2013/11/22	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH ONLY		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
		4 PLACES	±---	±---	DRAWN BY VOU	DATE 2013/11/12	MINI-CHANGE POWER ASSY 4P FEM/MAL ST/ST STD/ALT #14/4 BLACK PVC CABLE			
		3 PLACES	±---	±.005	CHECKED BY BARDEN	DATE 2013/11/12				
		2 PLACES	±0.13	±.010	APPROVED BY JFMURPHY	DATE 2013/11/22		MOLEX INCORPORATED		
1 PLACE	±0.25	±.020	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-130065-014	SHEET NO. 1 OF 1		
A	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								