

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300620281](#)  
**Status:** **Active**  
**Overview:** BradPower Cordsets and Receptacles  
**Description:** BradPower A-Size (7/8"-M22) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 14 AWG, Tri-Key, Black TPE Cable, 6.0m (19.68') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

Product Family Industrial Cordsets  
 Series [130062](#)  
 Connector End A BradPower A-Size (7/8"-M22)  
 Connector End B BradPower A-Size (7/8"-M22)  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [BradPower Cordsets and Receptacles](#)  
 Product Name BradPower A-Size  
 Protocol FF  
 Region Europe  
 Taxonomy Circular Industrial Cordsets  
 Type Double Ended  
 UPC 78172546646

**Physical**

Cable Diameter 9.47mm (.373")  
 Cable Length 6.0m (19.68')  
 Color - Cable Jacket Black  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Tri-Key  
 LED Indicator No  
 Material - Cable Jacket TPE  
 Material - Connector Body TPE  
 Material - Coupling Nut Black Epoxy Coated Zinc  
 Material - Plating Mating Gold  
 Net Weight 699.000/g  
 Orientation Straight to Straight  
 Poles 4  
 Temperature Range - Operating -20° to +90°C  
 Wire Size AWG 14  
 Wire/Cable Type TC-ER

**Electrical**


Current - Maximum per Contact 15.0A  
 Voltage - Maximum 600V

**Material Info**

Engineering Number 114130K21M060

**Reference - Drawing Numbers**

Sales Drawing SD-130062-022-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[130062 Series](#)

This document was generated on 10/31/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**