


## 1571982-2 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**1571982-2**

TE Part Number: 1571982-2

✓ [Active](#)

[Add to Part List](#)

### Slide Switches

✓ [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Number of Positions = 2
- Single Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Flush, Top
- Actuator Color = Black
- TSS Series

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [SLIDE SWITCH TSS11 AND TSS21 SERIES \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Number of Positions](#) = 2
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Actuator Style = Flush, Top
- Mount Angle = Vertical
- Termination Type = PC

#### Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

#### Body Related Features:

- Actuator Color = Black
- Series = TSS
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 3.30 [0.130]
- Actuator Material = Polyester
- Flammability Rating = UL 94V-0
- Length (mm [in]) = 10.20 [0.402]
- Width (mm [in]) = 5.23 [0.206]

#### Contact Related Features:

- Contact Plating = Gold
- Contact Material = Copper

#### Configuration Related Features:

- Terminal Configuration = Standard
- Operating Function = On None On
- Number of Actuators = Single

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Identification Marking:

- Stamped Marking = With

#### Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Need Help?](#)