



CONNECTORS

TRANSISTOR SOCKETS



✓ Active

TE CONNECTIVITY (TE)

8080-1G31=TRANSISTOR SOCKET AS

Augat | AD

8080-1G31

TE Internal Number: 4-1437504-3

Not EU RoHS Compliant

Not EU ELV Compliant

Number of Positions 3

Package TO-3

Lead Size Accepted 1.52 mm [.06 in]

Termination Method Solder

Operating Temperature Range (°C) -55 – 125

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

TRANSISTOR SOCKET

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration Contact

Package TO-3

Product Type Socket

Configuration Features

Number of Positions 3

Number of Solder Lugs 2

Body Features

Lead Size Accepted 1.52 mm [.06 in]

Color Green or Blue

Insulator Material Diallyl Phthalate (DAP)

Contact Features

Terminal Plating Tin-Lead

Termination Method Solder

Pin Diameter (in) .06

Terminal Material Beryllium Copper

Socket Type Transistor

Usage Conditions

Operating Temperature Range (°C) -55 – 125

Industry Standards

Insulator Flammability Rating UL 94V-0

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF

