

1825256 -6 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1825256 -6

✓ [Active](#)

Slide Switches

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Number of Positions = 3
- ? Single Pole - Three Throw Configuration (Pole - Throw)
- ? Actuator Style = Side
- ? Actuator Color = Black
- ? MHS Series

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [SLIDE SWITCH, MHS SERIES, SINGLE POLE, RIGHT ANGLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Number of Positions](#) = 3
- ? Configuration (Pole - Throw) = Single Pole - Three Throw
- ? Actuator Style = Side
- ? Mount Angle = Vertical
- ? Grade = Instrumentation
- ? Termination Type = PC
- ? PCB Retention Feature = Yes

Electrical Characteristics:

- ? Contact Rating = 300mA

Body Related Features:

- ? Actuator Color = Black
- ? Series = MHS
- ? Mount Style = Through -Hole
- ? Switch Style = Low Profile
- ? PCB Tail Length (mm [in]) = 3.51 [0.136]
- ? PCB Retention Method = Guide Posts
- ? Actuator Material = POM
- ? Flammability Rating = UL 94 -HB
- ? Actuator Travel = 2.00 [.079]

Contact Related Features:

- ? Contact Plating = Gold
- ? Contact Material = Copper Alloy

Configuration Related Features:

- ? Terminal Configuration = Standard
- ? Number of Actuators = Single

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = Alcoswitch