


COIL: ● +25 °C
 RESISTANCE 2640 OHMS ± 10%
 NOMINAL VOLTAGE 27-56 VDC
 MUST OPERATE 18.0 VDC
 MUST RELEASE 10.9 VDC MAX. 1.8 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 50 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX.
RELEASE 5 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/9/94 CK. 3/9/94

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. GENICOM
 CUST. NO. 3SAV5534M2

TYPE 'HMS' RELAY

HMS1230S07