


3SBC2091A2 Product Details



3SBC2091A2 (3-1617073-4)

TE Part Number: 3-1617073-4

 [Active](#)

 [Add to Part List](#)

Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 3SBC 1/5-Size Relay Series
- Input Voltage = 26.5 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 2 Amps.
- Non Polarized, Monostable Coil Magnetic System

[View all Features](#) |
 [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Termination Type = PC Pins

Electrical Characteristics:

- Input Voltage (VDC) = 26.5
- Contact Current Rating (Amps.) = 2
- Coil Polarity Protection Diode = Without
- Transistor Driver = Without
- Coil Resistance (Ω) = 1350
- MOSFET Driver = Without
- Coil Power Measurement = Milliwatts
- Coil Power, Nominal (mW) = 520
- Actuating System = DC
- Shock = 75 G's, 6ms
- Vibration = 30G's, 10 to 3000Hz

Body Related Features:

- [Series](#) = 3SBC 1/5-Size Relay

Contact Related Features:

- Mounting Options = PC Board
- Enclosure = Hermetically Sealed
- Approved Standards = M39016 Qualified, P Level

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Coil Magnetic System = Non Polarized, Monostable
- Coil Suppression Diode = With

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M39016/37-021P
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range (°C) = -65 - +125

Other:

- Brand = CII