


COIL: @ +25 °C  
 RESISTANCE 440 OHMS ± 10%  
 NOMINAL VOLTAGE 11.0-23 VDC  
 MUST OPERATE 6.65 VDC  
 MUST RELEASE 4.0 VDC MAX 0.66 VDC MIN

ENVIRONMENT:  
 VIBRATION 10 CPS TO 2500 CPS @ 20 g's  
 SHOCK 50 g's 11 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX  
RELEASE 5 MS MAX  
CONTACT BOUNCE 2 MS MAX

**CUSTOMER DATA SHEET**



CONTACT RATING: LOW LEVEL TO 2A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 12/22/92 CK 12/22/92



CUST. GENICOM  
 CUST. NO. 3SAV5004F2

TYPE "HMS" RELAY

**HMS1201S48**