

SSC22ABA Product Details



SSC22ABA (8-1437471-2)

TE Part Number: 8-1437471-2

 [Active](#)

 [Add to Part List](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- SSC Specification Grade Timing Series
- Time Delay Relay
- Input Voltage = 120 VAC
- Input Voltage = 120 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Time Delay Relay
- Termination Type = 11-Pin Octal Style Plug

Electrical Characteristics:

- Input Voltage (VAC) = 120
- Input Voltage (VDC) = 120
- Contact Rating = 10A Resistive @ 28 VDC/120 VAC

Body Related Features:

- [Series](#) = SSC Specification Grade Timing

Contact Related Features:

- Mounting Options = Socket
- Mode of Operation = Off-Delay
- Delay Time = 0.5 seconds to 15 seconds
- Type of Control = Knob
- Repeatability, Max. = ±1% +4 msec
- Approved Standards = CE Approved, CSA Certified, FM Approved
- Approx. Dimensions (L x W x H) (mm [in]) = 50.00 x 50.00 x 83.00 [1.970 x 1.970 x 3.270]

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range (°C) = -30 - +65

Other:

- Brand = Agastat