



8134-HC-12P2 Product Details

 **Live Product Chat** US Only
8:30am - 5pm ET, Mon - Fri



8134-HC-12P2
(5-1437514-9)
 [Active](#)

Discrete Sockets

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Socket
- Mating Pin Dia. Range = .89 - 1.14 mm
- Socket Length = 4.06 mm
- Gold Contact Spring Plating
- Production Application

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [HOLTITE CONTACTS](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

 THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

Product Specifications:

- [AUGAT* HOLTITE* Sockets](#) (PDF, English)

Application Specifications:

- [AUGAT HOLTITE Sockets](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Socket
- [Socket Length \(mm \[in\]\)](#) = 4.06 [0.160]
- [Sealant](#) = Without
- Proprietary Name = HOLTITE
- Recommended Hole Size (mm [in]) = 2.08 [0.082]

Body Related Features:

- [Mating Pin Dia. Range \(mm \[in\]\)](#) = 0.89 - 1.14 [0.035 - 0.045]
- Spring Material = Beryllium Copper

Contact Related Features:

- [Contact Spring Plating](#) = Gold
- [Contact Material](#) = Beryllium Copper

Configuration Related Features:

- [Insertion Method](#) = Hand/Semi-Automatic

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = Production

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP