


## 6-1437514 -7 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



### Discrete Sockets

[Always EU RoHS compliant but not ELV Compliant](#) ( [Find RoHS Compliant Alternates](#) / [Statement of Compliance](#) )

#### Product Highlights:

- ? Socket
- ? Mating Pin Dia. Range = .66 - .74 mm
- ? Socket Length = 3.51 mm
- ? Sleeve Style = Closed Bottom
- ? Tin-Lead Sleeve Plating

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**6-1437514 -7**  
(8134 -HC-5P3)  
 [Active](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [HOLTITE CONTACTS](#) (PDF, English)
- ? [CONTACT PLATED \(REF AUGAT 8134 -HC-5P2,P3\)](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? [AUGAT\\* HOLTITE\\* Sockets](#) (PDF, English)

#### Application Specifications:

- ? [AUGAT HOLTITE Sockets](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Product Type = Socket
- ? [Socket Length \(mm \[in\]\)](#) = 3.51 [0.138]
- ? [Sleeve Style](#) = Closed Bottom
- ? [Sealant](#) = Without
- ? Sleeve Material = Copper
- ? Recommended Hole Size (mm [in]) = 1.57 [0.062]

#### Body Related Features:

- ? [Mating Pin Dia. Range \(mm \[in\]\)](#) = 0.66 - 0.74 [0.026 - 0.029]
- ? Spring Material = Beryllium Copper

#### Contact Related Features:

- ? [Sleeve Plating](#) = Tin -Lead
- ? [Contact Spring Plating](#) = Tin Lead
- ? [Contact Material](#) = Beryllium Copper

#### Configuration Related Features:

- ? [Insertion Method](#) = Hand/Semi - Automatic/Automatic

#### Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS not ELV compliant

#### Operation/Application:

- ? Application = Production

#### Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

#### Other:

- ? Brand = AMP