

# › HMI Crouzet Touch - Performance Accessories for Millenium EVO & em4

- › TFT-LCD resistive touch screen
- › Ultra-slim format
- › Built-in isolated RS-485
- › PCB Coating Protection
- › Direct communication with M3 programming port
- › Modbus RS485 protocol (drivers for M3 and em4)
- › Modbus TCP/IP protocol (drivers for M3 and em4)
- › Integrated VNC server
- › Additional functions provided by Crouzet Touch programming software (e-mails, recipe database, enhanced security...)



CTP104-E  
Performance



CTP107-E  
Performance



CTP110-E  
Performance

Selection guide		
Type	Size	Part number
CTP104-E	4.3"	88 970 554
CTP107-E	7"	88 970 564
CTP110-E	9.7"	88 970 574

Accessories	
Description	Part number
Modbus RTU RS485 interface to CTP104-E	88 980 171
Modbus RTU RS485 interface to CTP107-E and CTP110-E	88 980 172
Modbus RTU RS485 Millenium 3 expansion to CTP104-E	88 970 503
Modbus RTU RS485 Millenium 3 expansion to CTP107-E and CTP110-E	88 970 504
Crouzet Touch Soft + programmation cables	88 970 591

	CTP104-E	CTP107-E	CTP110-E
<b>Specific characteristics</b>			
Part number	88 970 554	88 970 564	88 970 574
Type	CTP104-E	CTP107-E	CTP110-E
Size	4.3"	7"	9.7"
Resolution	480 x 272	800 x 480	1024 x 768
Brightness	400 cd/m <sup>2</sup>		350 cd/m <sup>2</sup>
On front panel color	Pantone Process Black C, Blue Pantone 285C		
Power consumption	300 mA @ 24 V, 88 mA @ 24V (backlight OFF)	450 mA @ 24 V, 92 mA @ 24V (backlight OFF)	650 mA @ 24 V, 162 mA @ 24V (backlight OFF)
Colors	16.7 M		262 K
LCD viewing angle (Top/Bottom/Left/Right)	30/50/50/50	70/50/70/70	60/70/70/70
Processor	32Bit RISC Cortex-A8, 600 MHz		32Bit RISC Cortex-A8, 1 GHz
Storage memory	128 MByte		512 MByte
RAM memory	128 MByte		256 MByte
USB	Host USB 2.0		
Ethernet	RJ45 type, 10/100 Mbit/s, MDI/MDIX		2 x RJ45 type, 10/100/1000 Mbit/s, MDI/MDIX

	CTP104-E	CTP107-E	CTP110-E
Port RS232	COM1 male		COM1 male, COM3 male. Only Tx & Rx (no RTS/CTS) may be used for COM1 when COM3 is also used.
Port RS485	COM1 2/4 Wires male, COM3 2 Wires male		COM2 2/4 Wires female, COM3 2 Wires female
CAN bus	N/A		CANopen Protocol
UL Certification	cULus Listed		N/A
Weight	Approximately 0.25 kg	Approximately 0.6 kg	Approximately 0.85 kg
Dimensions (W x H x D)	128 x 102 x 32 mm / 5.04 x 4.02 x 1.26"	200.3 x 146.3 x 34 mm / 7.89 x 5.77 x 1.34 "	260.6 x 203.1 x 36.5 mm / 10.26 x 8 x 1.44 "
Vesa Mount	N/A		75 x 75 mm / 2.95 x 2.95"
Panel cutout	119 x 93 mm / 4.69 x 3.66"	192 x 138 mm / 7.56 x 5.43 "	250 x 192 mm / 9.84 x 7.56 "
PCB Coating	Yes		

**General characteristics**


Enclosure	Plastic		
Products certification	CE		
Nominal voltage	24 V <sub>DC</sub> (-20% / +20%)		
Operating limits	19.2 - 28.8 V <sub>DC</sub>		
Power isolation	Yes		
Power supply earthing	Yes		
Voltage resistance	500 V <sub>AC</sub> (1 minute)		
Isolation resistance	> 50 Mohms at 500 V <sub>DC</sub>		
Vibration endurance	10 to 25 Hz (X,Y,Z direction 2G 30 minutes)		
Conducted and radiated emissions	EN 55022: 2010 +AC: 2011 class A CISPR 22: 2008	EN 55022: 2010 +AC: 2011 class B CISPR 22: 2008	EN 55022: 2010 +AC: 2011 class A CISPR 22: 2008
Electro-Magnetic Interference, harmonic current	EN 61000-3-2: 2014		
Electro-Magnetic Interference, voltage flicker	EN 61000-3-3: 2013		
Resistance to electrostatic discharge	Immunity to ESD IEC/EN 61000-4-2: 2008		
Resistance to HF interference (Immunity) (EN55024: 2010)	Immunity to radiated electrostatic fields IEC/EN 61000-4-3: 2010 Immunity to fast transients (burst immunity) IEC/EN 61000-4-4: 2012 Immunity to shock waves IEC/EN 61000-4-5: 2014 Radio frequency in common mode IEC/EN 61000-4-6: 2013 Immunity to magnetic field IEC/EN 61000-4-8: 2009		
Voltage dip, interruption	IEC/EN 61000-4-11: 2004		
Protection against electric shock	Class II equipment		
Mount	Built-in, fixing by screw clamps (supplied) for 1 to 6 mm panel		
Connection	Removable 3-pin screw terminal block (supplied)		
Protection rating	NEMA4 / IP 65 Compliant front panel		
Operation temperature	0 (32 °F) → +50 °C (122 °F)		
Storage temperature	-20 (-4 °F) → +60 °C (140 °F)		
Relative humidity	10 → 90% max. (no condensation or dripping water)		

**Display**


Type	TFT LCD
Contrast ratio	500: 1
Backlight type	Led
Backlight life time	> 30.000 Hours
Touch panel: type	4 wires resistive, with user-definable layout
Touch panel: key life	1 million operations minimum
Accuracy	Active Area Length(X)±2%, Width(Y)±2%
Driver Millenium 3	SLIN/SLOUT 24 V <sub>DC</sub> , XN05, XN06

	CTP104-E	CTP107-E	CTP110-E
Driver em4	Modbus RS485 & TCP/IP		
Driver Modbus IDA	ASCII, RTU & TCP/IP		
RTC	Use Millenium 3, em4 or build-in clock		
RTC battery	CR2032		
RTC time life battery	> 5 years, not rechargeable		


**Schemes**  
**Dimensions**  
**CPT104-E**



**Panel cutout**





**Connexion**




a	Power Connector
b	COM1 RS232, RS485. COM3 RS485
c	USB Host
d	Ethernet

**CPT107-E**






**Panel cutout**







**Connexion**




c	Power Connector
d	COM2 RS485. COM3 RS485
e	USB Host
f	COM1 RS232
g	Ethernet


**CPT110-E**



**Panel cutout**



**Connexion**



c	Power Connector
d	COM2 RS485. COM3 RS485
e	COM1 RS232. COM3 RS232
f	USB Host
g	Ethernet LAN 2
h	Ethernet LAN 1

**Warning:**

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet Automatismes SAS and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.