

Power PCB Relay RT2 bistable

- 2 pole 8A, 2 form C (CO) contacts
- Polarized bistable version with 1 or 2 coils
- 5kV/10mm coil-contact
- Reinforced insulation

Typical applications Battery powered equipment or applications with "memory function".



coils	1 coil	2 coils

Coil Data, bistable coils	1 coil	2 coils
Magnetic system	polarize	d, bistable
Coil voltage range	3 to 4	48VDC
Operative range, IEC 61810		2
Limiting voltage, % of rated coil voltage	ge 120%	150%
Min./Max. energization duration	30ms/1min at -	<10% duty factor
Coil insulation system according UL	cla	iss F


Coil versions, bistable coil


0-1	Dete el	0-+	Deeet	0-1	Datadaall		
Coil	Rated	Set	Reset	Coil	Rated coil		
code	voltage	voltage	voltage	resistance	power		
	VDC	VDC	VDC	Ω±10%	mW		
bistable	1 coil						
A03	3	2.1	1.7	21	429		
A05	5	3.5	2.8	62	403		
A06	6	4.2	3.3	90	400		
A12	12	8.4	6.6	360	400		
A24	24	16.8	13.2	1440	400		
A48	48	33.6	26.4	5520	417		
bistable	2 coils						
F03	3	2.1	1.7	15	600		
F05	5	3.5	2.8	42	595		
F06	6	4.2	3.3	55	655		
F12	12	8.4	6.6	240	600		
F24	24	16.8	13.2	886	650		
F48	48	33.6	26.4	3291	700		
All figures	All figures are given for coil without pro-operaization, at ambient temporature, 23°C						

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.

Bistable coils - operation

Version	1 (coil	2 coils
Coil terminals	A1	A2	A1 A3 A2
Operate	+	-	+ -
Reset	-	+	- +
Contact position not defined at delivery			





03-2022, Rev. 0322 www.te.com © 2014 Tyco Electronics Corporation, a TE Connectivity Ltd. company.

Catalog and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Catalog and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Catalog product data, 'Definitions' section, application notes and all specifications are subject to change.

1

Approvals VDE Cert. No. 40007571, UL E214025, cCSAus 1142018

Technical data of approved types on request.

Contact Data

Contact Data		
Contact arrangement	2 form C (CO)	
Rated voltage	250VAC	
Max. switching voltage	400VAC	
Rated current	8A, UL: 10A	
Limiting continuous current	8A, UL: 10A	
Limiting making current, max. 4s, duty facto	r 10% 15A	
Breaking capacity max.	2000VA	
Contact material	AgNi 90/10	
Frequency of operation, with/without load	900/72000h-1	
Operate/Reset time max.	10/5ms	
Bounce time max., form A/form B	4/9ms	

Contact ratings

Contact	ratings		
Туре	Contact	Load	Cycles
IEC 6181	0		
RT444	A (NO)	8A, 250VAC resistive, 85°C	100x10 ³
RT424	C (CO)	8A, 250VAC resistive, 85°C	30x103
UL 61810	-1 (former UL	508)	
RT424	A/B (NO/NC)	10A, 250VAC, general purpose, 85°C	20x10 ³
RT424	A/B (NO/NC)	1/2hp, 240VAC ,85°C	1x10 ³
RT424	A/B (NO/NC)	Pilot duty, B300, R300, 85°C	6x10 ³
RT4/E	A/B (NO/NC)	10A/24VDC, general purpose, 85°C	5x10 ³
EN60947	-5-1		
RT424	A/B (NO/NC)	AC-15, 250VAC, 3A	6.050

Mechanical endurance

Max


300 200

100

а 10

S015

30 voltage [30 >2x10⁶ operations



250VAC esistive load AgNi90/1 10 12 14 16 Switching current [A]



SCHRACK

Power PCB Relay RT2 bistable (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	1000V _{rms}
between contact and coil	5000V
between adjacent contacts	2500V_ms
Clearance/creepage	
between contact and coil	≥10/10mm
between adjacent contacts	≥ 3/4mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI 250V

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature	
bistable 1 coil	-10 to 85°C
bistable 2 coils	-40 to 85°C
Category of environmental protection	
IEC 61810	RTII - flux proof
	RTIII - wash tigth
Vibration/shock resistance (functional),	
opening B contact	3/5g
opening closed A contact	6/15g
Shock resistance (destructive)	100g

Other Data (continued) Terminal type PCB-THT, plug-in¹⁾ Weight 1<u>3g</u> Resistance to soldering heat THT 270°C/10s IEC 60068-2-20 Packaging/unit tube/20 pcs., box/500 pcs 1) socket available for 1 coil version only, see Accessories.


Accessories

For 1 coil version,

details see datasheet Accessories Industrial Power Relay RT NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.

PCB layout / terminal assignment

Bottom view on solder pins



Product code	Version	Contacts	Contact material	Coil version	Coil	Part number
RT424A05	8A,	2 form C (CO)	AgNi 90/10	Bistable 1coil	5VDC	4-1393243-4
RT424A12	pinning 5mm,	contacts			12VDC	4-1393243-6
RT424F05	flux proof			Bistable 2 coils	5VDC	5-1393243-2
RT424F12					12VDC	5-1393243-4
RT424F24					24VDC	5-1393243-6
RT424F48					48VDC	5-1393243-7
RTE24F24	8A	2 form C (CO)	AgNi 90/10	Bistable 2 coils	24VDC	8-1415541-7
RTE24F06	pinning 5mm				6VDC	1-1415020-1
RTE24F12	wash tight				12VDC	7-1415072-1

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request.

03-2022, Rev. 0322 www.te.com © 2014 Tyco Electronics Corporation, a TE Connectivity Ltd. company.

2

Catalog and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Catalog and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Catalog product data, 'Definitions' section, application notes and all specifications are subject to change.