

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200652249](#)  
**Status:** **Active**  
**Overview:** Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable  
**Description:** Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Female (Straight) to Pigtail, 22 AWG, Unshielded WSOR Cable, 5.0m (16.40') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120065](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Brass  
 Overview [Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable](#)  
 Product Name Micro-Change (M12)  
 Protocol N/A  
 Region Europe  
 Type Single Ended  
 UPC 887191554631

**Physical**

Cable Diameter 4.80mm (.189")  
 Cable Length 5.0m (16.40')  
 Color - Cable Jacket Black  
 Coupling Style Knurled Hexnut, Threaded  
 Gender Female-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket TPU  
 Material - Connector Body TPU  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold  
 Net Weight 477.000/g  
 Orientation Straight to Pigtail  
 Poles 3  
 Temperature Range - Operating -25°C to +85°C  
 Wire Size AWG 22  
 Wire/Cable Type UL 21215

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 60V

**Material Info**

Engineering Number 803000B30M050

**Reference - Drawing Numbers**

Sales Drawing 1200652251-00P



**EU ELV**

**Compliant with Exemption 3**

**EU RoHS**

**Compliant with Exemption 6(c)**

**China RoHS**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant with

Exemption 3

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[120065 Series](#)

This document was generated on 08/26/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**